Straight Blade Devices 20A, 250V, 2 Pole, 3 Wire Grounding Valise® Connector Body

HUBBELL

Features

- Hinged one piece body design for easy assembly
- Powerful, offsetting cord grips clamp on individual conductors
- Assembly screws are captive and will not fall out while wiring

Ordering Information

Description	Cord Diameter .220"660"(5.6-16.	UPC	Catalog Number
Yellow nylon		783585013190	HBL5469VY
	0)		



UL Listed to UL498 File E1706 CSA Certified to C22.2 No. 42 File 280C NEMA® WD-6 Compliant

Specifications

Housing Nylon
Contacts Brass
Assembly Screws Plated Steel
Cable Inserts PPO

Terminal Screws #8-32 Brass , multiple drive

Terminal Clamp Nickel plated steel
Assembly Screws Plated steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device Terminal Accommodation #18-#12 AWG stranded copper wire only

Terminal Identification Terminals identified in accordance with UL 498 and CSA


Environmental

Flammability UL 94 HB or better

IP Suitability IP20

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)





Resources

Customer Use Drawing eCatalog

