



Main

Range	TeSys TeSys Deca
Device short name	GVAN
Product or Component Type	Auxiliary contact block
Product Compatibility	GV2ME GV3P GV2RT GV2LE GV2L GV3L GV2P
Mounting Location	Left side
Pole contact composition	2 NO

Complementary

[Ui] rated insulation voltage	600 V UL 508 690 V IEC 60947-1 600 V CSA C22.2 No 14
[Ue] rated operational voltage	48...690 V AC 24...240 V DC
[Ith] conventional free air thermal current	6 A
Protection type	GB2CB... circuit breaker GG fuse 10 A
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Rated operational power in VA	300 VA 48 V AC-15 100000 cycles 414 VA 690 V AC-15 100000 cycles 500 VA 110...127 V AC-15 100000 cycles 500 VA 500 V AC-15 100000 cycles 650 VA 440 V AC-15 100000 cycles 720 VA 230...240 V AC-15 100000 cycles 850 VA 380...415 V AC-15 100000 cycles
Rated operational power in W	120 W 240 V DC-13 100000 cycles 140 W 110 V DC-13 100000 cycles 140 W 24 V DC-13 100000 cycles 180 W 60 V DC-13 100000 cycles 240 W 48 V DC-13 100000 cycles
Tightening torque	12.39 lbf.in (1.4 N.m) screw clamp terminals
Height	3.50 in (89 mm)
Width	0.37 in (9.3 mm)
Depth	2.60 in (66 mm)
Net Weight	0.11 lb(US) (0.05 kg)
Color	Dark grey

Environment

Environmental characteristic	Normal environment
Product Certifications	UKCA

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	3389110343502
Nbr. of units in pkg.	1
Package weight(Lbs)	1.55 oz (44 g)
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.75 in (1.9 cm)
Package 1 width	5.04 in (12.8 cm)
Package 1 Length	5.51 in (14 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	17.78 oz (504 g)
Package 2 Height	3.74 in (9.5 cm)
Package 2 width	3.94 in (10 cm)
Package 2 Length	6.10 in (15.5 cm)
Unit Type of Package 3	S02
Number of Units in Package 3	60
Package 3 Weight	7.43 lb(US) (3.37 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

GVAN20

