



### Main

Range	TeSys
Product or Component Type	Enclosure
Device short name	GV2MC
Accessory / separate part category	Mounting accessory
Product Compatibility	GV2ME
Enclosure type	Surface mounting

### Complementary

Auxiliary mounting location	Right Left
Height	5.79 in (147 mm)
Width	3.66 in (93 mm)
Depth	3.31 in (84 mm)
Net Weight	0.66 lb(US) (0.3 kg)

### Environment

IP degree of protection	IP55 41 °F (5 °C)
Environmental characteristic	Standard environment
Product Certifications	UKCA

### Ordering and shipping details

Category	18402 - WORLD SERVICE PARTS(CONTROL ACCESS)
Discount Schedule	CP10
GTIN	3389110213669
Nbr. of units in pkg.	1
Package weight(Lbs)	10.34 oz (293 g)
Returnability	Yes
Country of origin	CZ

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.70 in (9.4 cm)
Package 1 width	3.86 in (9.8 cm)
Package 1 Length	6.10 in (15.5 cm)
Unit Type of Package 2	S04
Number of Units in Package 2	27
Package 2 Weight	19.25 lb(US) (8.733 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	15.75 in (40 cm)
Package 2 Length	23.62 in (60 cm)
Package 3 Height	30.31 in (77 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------