



Main

Range of Product	9049
Product or Component Type	Float kit

Complementary

Product Compatibility	9036G 9038A 9036D
Kit composition	1 float 2 stop 2 rod
Rod length	5 ft (1.52 m) stainless steel 304
Type of float	Float tapped at top stainless steel 304
Condition of use	Maximum recommended tubing length: 12.5 ft
Net buoyancy	60 ozf in water
Product Weight	3 Oz (85.05 g) total weight of stops 16.9 Oz (479.12 g) weight of 5 ft rod 3.4 Oz (96.39 g) weight of extra rod (per ft) 5.6 lb(US) (2.54 kg) total weight

Ordering and shipping details

Category	21617 - 9049 ACCESSORIES (DISCOUNT CP7G)
Discount Schedule	CP7G
GTIN	785901597360
Nbr. of units in pkg.	1
Package weight(Lbs)	5.15 lb(US) (2.34 kg)
Returnability	No
Country of origin	MX

Packing Units

Package 1 Height	77.47 in (196.774 cm)
Package 1 width	30.50 in (77.470 cm)
Package 1 Length	196.77 in (499.805 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------