



Ultra-Inlet Guard[®] Specifications

Minimum Average Fabric Values

Properties	ASTM Test	Value
Mass per Unit Area (oz/yd ²)	D-3776	5.2
Grab Tensile Strength, MD x CD (lbs)	D 4632	297 x 223
Grab Elongation, MD x CD (%)	D 4632	58 / 59
Trapezoid Tear, MD x CD (lbs)	D 4533	81 x 75
Puncture (lbs)	D 4833	99
Burst Strength (psi)	D 3786	340
Permittivity (sec-1)	D 4491	2.60
A.O.S. (U.S. sieve – (mm))	D 4751	60
Water Flow Rate (gpm/ft ²)	D-4491	192

Revised 08.21.07