

100 FOOT INDOOR/OUTDOOR NON ELECTRIC EXIT SIGN

UL 924 Listed



- Listed to UL 924 and meets NFPA Life Safety Code 101
- 100 foot rated for visibility and readability in indoor, outdoor, and even wet conditions
- Can be charged with fluorescent, metal halide or mercury vapor light
- 25+ Years life expectancy
- Can be used for both high-level and low-level applications
- Worry free — no maintenance checks, always works when needed
- Easy Installation and removal
- Zero energy consumption — no bulbs or battery replacement
- Green design — non-toxic, non-radioactive, no disposal costs
- Designed for surface, flag, ceiling, or conduit mounting
- Immediately visible during emergency or blackout conditions
- LEED point contributor
- The preferred energy-savings choice for large, open facilities such as big-box retailers, Federal government buildings, manufacturing plants and warehouse facilities

SKU NO.	DESCRIPTION	W	H
3EYL4	Green Single Sided Photoluminescent 100ft. Exit Sign	8.5	16
3EYL5	Green Double Sided Photoluminescent 100ft. Exit Sign	8.5	16



SKU NO.	DESCRIPTION	W	H
3EYL2	Red Single Sided Photoluminescent 100ft. Exit Sign	8.5	16
3EYL3	Red Double Sided Photoluminescent 100ft. Exit Sign	8.5	16



SKU NO.	DESCRIPTION	W	H
3EYL6	Black Single Sided Photoluminescent 100ft. Exit Sign	8.5	16
3EYL7	Black Double Sided Photoluminescent 100ft. Exit Sign	8.5	16



The Grainger Choice badge signals a broad selection of products that deliver quality and value, brought to you by Grainger.

