



WORKSAFE 2206
GRAINGER #3KXN5 | 6V SAFETY ORANGE LANTERN

MSHA APPROVED, LIGHTWEIGHT DURABLE LANTERN WITH A RUNTIME OF 15 HOURS

- IPX7 rated, waterproof and can float!
- Krypton Bulb
- Tuflex® lens
- Spare bulb compartments
- Switch guard protects switch on impacts
- Oversized reflector for more light output
- Glove size handle
- Circuit breaking mechanism
- Optional stand



LIGHTWEIGHT, WATERPROOF,
AND AFFORDABLE
WORKSAFE LANTERN

SPECIFICATIONS

POWER SOURCE: Alkaline or Carbon Zinc 6V
Lantern Battery

LAMP/BULB: KPR 113

PEAK BEAM INTENSITY: 50,000 candela

BEAM DISTANCE: 165 Meters

RUN TIME: 15 Hours

WEIGHT: 14 oz without batteries

LENGTH: 8.2 in. **WIDTH:** 4.9 in. **Height:** 5.6 in.

COLORS: Safety Orange, Black Lens Rim

MASTER PACK

WEIGHT: 5.8 lbs. (2.6 kg)

CUBE: 0.93 ft³ (0.02 m³)

QUANTITY: 6

KBS MODEL: #07050 (Grainger #3KXN5)

UPC-IC (12 Digit): 01673070502

KBS ACCESSORY: #20414- KPR 113 Bulb

SAFETY RATINGS

UL/CUL: Class I, Div I, Group C & D

Class II, Div I, Group G

Operating Temp T3B

Class I Zone I Group IIB & IIA

MSHA Approved



Marmon
Holdings, Inc.
A Berkshire Hathaway Company

See it all.™

