




## 45 DEGREE CONDUIT AND CORD CONNECTORS - STEEL/MALLEABLE IRON

45 Degree Connectors Steel/Malleable Iron  
N/A

B47.1



Catalog #: 3566

### APPLICATIONS

For use in outdoor or indoor locations on flexible metallic liquidtight conduit and Type B flexible nonmetallic liquidtight conduit  
Use to positively bond the conduit to a box or enclosure

### PRODUCT FEATURES

RACO liquidtight connectors are suitable for use in Class I, Div. 2, Class II, Div. 1 & 2; and Class III, Div. 1 & 2 hazardous locations  
Patented split gland-ring is designed to slip onto the conduit quickly gripping the jacket of the conduit, speeding installation, assuring a perfect seal, and preventing pullouts  
All components are reusable - RACO liquidtight connectors may be easily disassembled and reused after years of service  
Sealing washer (included) provides a liquidtight seal when terminating the connector in a threadless opening  
Heavy duty locknut included with every RACO liquidtight connector assures continuity of ground  
UPC bar coded fittings are individually polybagged with a preprinted UPC-A bar code, and packaged in pre-scored tear top cartons for an attractive presentation  
All steel/iron components are zinc electro plated for added corrosion protection  
3/8 in. to 2 in. Malleable iron bodies  
3/8 in. to 1 in Steel nuts, 1-1/4 in. to 4 in. Malleable iron nuts  
N/A

### UL LISTED

Standard 514B, UL Listed E195969

### CSA

C22.2 No. 18

### GENERAL PRODUCT INFORMATION

Sub Class: Insulated  
Trade Size: 1-1/2 in.

### DRAWING DIMENSIONS

Dimension A: 2-3/8 in.  
Dimension B: 47/64 in.  
Thread Spec. B: 1-1/2 in. - 11-1/2 NPT  
Dimension C: 2 in.  
Dimension D: 1-9/16 in.

### PACKAGING

Package Type: Carton  
Ship Carton Qty.: 5  
Product UPC-A Labeled: No  
Weight (Lbs. Per/C): 123.50  
Ship Carton Length (in.): 7.38  
Ship Carton Width (in.): 5.75  
Ship Carton Height (in.): 4.75  
Ctn Weight (Lbs.): 6.18  
UPC Number: 050169035665  
I2of5: 50050169035660