



Hi-Strength 90 Spray Adhesive

Technical Data

March 2015

Product Description

An industrial grade spray adhesive that is typically used for bonding HPL to wood.

Key Features

- A high strength, fast, contact-type adhesive
- Excellent adhesive for decorative laminates, particleboard, and many other materials, even polyethylene, polypropylene, and SBR rubber
- Has excellent heat resistance

Typical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product	3M™ Hi-Strength 90 Spray Adhesive	3M™ Hi-Strength 90 Cylinder Spray Adhesive	3M™ Hi-Strength 90 Spray Adhesive (Bulk)
Base:	Synthetic Elastomer	Synthetic Elastomer	Synthetic Elastomer
Solids Content - (by wt.):	13%	13%	23%
Density (lbs/gal):	6.0	5.7	6.4
Viscosity (cps):	N/A	N/A	100-500
Color(s):	Translucent	Translucent	Translucent
Volatile Organic Compounds (VOC):	< 55%	571 g/L	356 g/L
Hazardous Air Pollutants (HAPS) % wt (calculated):	<0.4%	No	No
CARB Compliant:	Yes	N/A	N/A
SCAQMD 1168 Compliant:	N/A	No	No
GREENGUARD Indoor Air Quality Certified®:	No	No	No
LEED® Eligible:	Yes	No	No
Coverage @ 2.5 gms /ft ² per lb (sqft):	23.6	23.6	42
Spray Pattern:	Variable Lace	Lace	Lace
Dry Time:	1 minute	1 minute	1 minute
Bonding Range:	1-10 minutes	1-10 minutes	1-10 minutes
Shear Adhesion Failure Test - SAFT ⁽¹⁾ :	250F	250F	250F
Flammable Solvent:	Yes	Yes	Yes
Flammable Propellant:	Yes	Yes	N/A

⁽¹⁾SAFT Shear Adhesion Failure Test with birch plywood, 1 inch overlap, 100 grams used, temperature start at 90F and ramped 10F every 10 mn. until complete failure.

Available Sizes

Container Size	3M Stock Number	UPC Number
24 Fl. Oz. (Net Wt. 17.6 oz) - Aerosol	62-4942-4950-1	00-021200-30023-3
24 Fl. Oz. (Net Wt. 16.9 oz) - Inverted Aerosol	62-4942-4970-9	00-051111-07278-3
Large Cylinder - 28.8 lbs.	62-4994-8030-9	00-021200-41554-8
Intermediate Cylinder - 141.6 lbs.	62-4994-8150-5	00-051115-25774-2
Jumbo Cylinder - 283.2 lbs.	62-4994-8300-6	00-051115-25775-9
5 gallon pail - 32.5 lbs.	62-4479-8532-6	00-021200-43797-7
54 gallon drum - 338 lbs.	62-4479-9532-5	00-021200-43814-1

3M

Hi-Strength 90 Spray Adhesive

Storage	Store product at 60°-80°F (16°-27°C) for maximum storage life. Higher temperatures reduce normal storage life. Lower temperatures may cause increased viscosity of a temporary nature. Rotate stock on a “first in-first out” basis.
Shelf Life	When stored at the recommended conditions in original, unopened container, this product has a shelf life of 15 months from date of shipment.
Precautionary Information	Refer to product label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.
Technical Information	The technical information, recommendations and other statements contained in this document are based upon testes or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.
Product Use	Many factors beyond 3M’s control and uniquely within user’s knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user’s method of application.
Warranty, Limited Remedy, and Disclaimer	Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOMER OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M’s option, replacement of the 3M product or refund of the purchase price.
Limitation of Liability	Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Industrial Adhesives and Tapes Division
3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/Adhesives

3M is a trademark of 3M Company.
The GREENGUARD INDOOR AIR QUALITY
CERTIFIED Mark is a registered certification
mark owned by Air Quality Sciences, Inc. and
used under license through the Greenguard
Environmental Institute. LEED® is a registered
trademark of the United States Green Building Council (USGBC).
©3M 2015