



Nitrile

## White nitrile exam glove with HYDRASOFT™ Skin Moisturizing Technology

- Designed with our patented HYDRASOFT™ Skin Moisturizing Technology which is proven to allow skin to retain 2X more moisture\* than gloves without HYDRASOFT™
- Soft nitrile formulation provides a comfortable fit and feel
- Thin and lightweight to ensure excellent tactility



NOW FEATURING  
**HYDRASOFT™**  
Skin Moisturizing Technology

### Industries

- Healthcare
- Life Sciences
- Food Processing

### Recommended For

- Sample taking and processing
- Protection from Type I latex allergy in HCW's or patients
- Standard patient examinations
- Enhanced tactile sensitivity and dexterity, especially for delicate procedures
- Oral examinations
- Food contact
- Laboratory analysis
- Testing
- Helping protect skin from drying or cracking
- Pharmaceutical manufacturing
- General dentistry



### TECHNICAL DATA SHEET

#### PRODUCT INFORMATION

	Soft White Nitrile TQ-601
<b>Material</b>	Nitrile
<b>Color</b>	White
<b>Glove Design</b>	Chlorinated, Coated with HYDRASOFT™ Technology, Powder-Free, Textured Fingers
<b>Cuff</b>	Beaded
<b>Regulatory/Standards Compliance</b>	ASTM D6319, EN 420:2003 + A1:2009, EN 455 1-4, EN ISO 13485, FDA21 CFR 177-2600, US QSR/FDA 510(k) Medical Examination Grade
<b>Packaging</b>	100 gloves per dispenser 10 dispensers per case 1000 gloves per case
<b>Country of Origin</b>	Indonesia
<b>User Needs Segment</b>	High Touch
<b>Available sizes</b>	XS (5.5 - 6), S (6.5 - 7), M (7.5 - 8), L (8.5 - 9), XL (9.5 - 10)
<b>Anti-static</b>	Not Tested

#### PHYSICAL PROPERTIES

	Typical Values		Testing Method
Length (mm/inches)	240 / 9.5		ASTM D3767, EN 420
Freedom from Holes (Inspection level I)	1.5 AQL		ASTM D5151, EN 455-1
Palm Thickness (mm/mils)	0,07/2,8		ASTM D3767, EN 420
Finger Thickness (mm/mils)	0,10/3,9		ASTM D3767, EN 420
	BEFORE AGING	AFTER AGING	
Ultimate Tensile Strength (MPa)	24	26	ASTM D412 & D573
Elongation at Break (%)	500	400	ASTM D412
Force at break (N)	7	7	

#### ORDERING INFORMATION

Size	XS (5.5 - 6)	S (6.5 - 7)	M (7.5 - 8)	L (8.5 - 9)	XL (9.5 - 10)
<b>Product Code</b>	TQ-601-XS	TQ-601-S	TQ-601-M	TQ-601-L	TQ-601-XL

#### Technology



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Russia

Ansell PYC  
Ten. +7 495 258 13 16

Ansell, <sup>®</sup> and <sup>™</sup> are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.