



# Product Data Sheet

## Part # 8068 Ultra-Pop Up Pool 66 Gallon



Pop up pools instantly expand to capture leaks from saddle tanks, pipes, hydraulic lines, and many other industrial incidents

Ultra-Pop Up Pools are available in 400, 250, 150, 100, 66, and 20 gallon sizes. Choose Sprung Steel or Economy Models<sup>+</sup> to meet your needs. Simply give them a quick shake — they instantly expand and are ready for response to any emergency.



- + Unique, Patented Design – foam ring rises with level of liquid to raise side-walls.
- + Compact folded size – stores efficiently inside spill kits; handles on storage bag<sup>\*</sup> can also be used to hang on a wall near shipping/receiving docks
- + Excellent chemical resistance, including diesel fuel, antifreeze, acids, caustics, and corrosives.
- + Helps minimize environmental damage and related clean-up costs.
- + Excellent for response to damaged saddle tanks and cross-over lines, hazmat spills, leaking containers, machinery, and piping.
- + Other applications include use as a decontamination pool and collection pool for soiled sorbents.

U.S. Patent No. 5,429,437

Part#	Description	Dimensions (Filled) in. (mm)	Weight lbs. (kg)
8068	Economy Model 66 gal (250 L)	Wall Height 12, Top dia. 42, Bottom dia. 53 (305, 1067, 1347)	4.0 (2.0)

### Specifications

Sump Capacity:	66 gal.
Containment Type:	Containment Pools/Pads
Folded Dimensions:	24" Dia. x 8" L Folded
Sump Dimensions:	Top: 42" Dia. / Bottom: 53" Dia. x 12" H
Usable Floor Space:	53" Dia. Floor Space
Wall Type:	Self-Rising
Sold as:	1 each
Max on Pallet:	100
Composition:	10 mil PE
UPC Code:	80841608068