



## SPECIFICATIONS

Product Description: **HEATER**  
Part Number: **9401-50**  
Style: **ELECTRIC**

### GENERAL DESCRIPTION:

The lightweight Tent Heater offers the rugged, heavy duty design of all steel housing with all-enclosed tube heating elements and a sealed motor for maximum durability. This powerful heater will raise the air temperature in an Allegro Work Tent by approximately 50°F (10°C).



### CONSTRUCTION:

- Rigid metal housing
- Powder coated green
- Metal grid exhaust outlet
- Plastic handle
- 5 blade fan

### FEATURES:

- Lightweight portable heater
- CSA Approved and UL Listed
- User friendly and proven reliability
- Easy to adjust thermostat knob (32°F to 100°F) (0°C to 37.7°C)
- High quality sealed motor
- Overheat protection to ensure safe and effective use

### MOTOR:

- 120 Volt
- Single Phase, 60 Hz
- 13 Amps

### BURNING RATING:

- 1500 Watts of 5,000 BTU heating power with 115 CFM (195.38 m<sup>3</sup>/hr) air flow

### POWER CORD:

- 9' (2.75 m) AWG 3/16 Integrated NEMA 5-15, 3 Prong plug

### DIMENSIONS:

Length In (cm)	Width In (cm)	Height In (cm)	Weight Lbs (Kg)
12" (30.4 cm)	8" (20.3 cm)	12" (30.4 cm)	14 lbs (6.3 kg)