

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-920

Light duty oil repellent, oil grip multi-purpose glove



Oil

LD

Light Duty

## High performance grip and oil repellence

- Multi-layer coating provides high abrasion resistance and increases wear life
- Ergonomic, natural fit along with superior dry and oil grip for high productivity
- Durable material is machine launderable for extended life and reduced replacement costs



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

### Applications

- Assembly & inspection of components
- Production line support & maintenance
- Seizing structural parts
- Fabricating metal parts, glass sheets
- Applying finish to materials, products

# HyFlex®

ADVANCED MECHANICAL PROTECTION

## 11-920

Light duty oil repellent, oil grip multi-purpose glove

### Key Features

- HyFlex® 11-920 glove provide high performance grip and oil repellence when working in oily environments
- ANSELL GRIP™ Technology contains microscopic channels in the glove coating to displace oil, resulting for a more secure grip when handling oily parts
- RIPEL™ Liquid Repellence Technology creates a liquid impermeable layer to prevents oil or lubricant from making contact with the wearer's skin, enhancing hand health
- Seamless knit design provide an outstanding fit, comfort and dexterity to maximize all-day productivity
- Also available in vend pack

### Technologies



### Performance Standards & Regulatory Compliance



EN 388:2003



3131

EN 388:2016



3131A

REACH Compliant

### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLO R	PACKAGE
HyFlex® 11-920	Palm Coated, Nitrile, Nylon, Knitwrist	15	6, 7, 8, 9, 10, 11	208-270 mm/ 8.18-10.62 inches	Blue	• 12 pairs in a bag; 12 bags in a carton



For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada Inc.  
105, rue Lauder  
Cowansville (Québec)  
J2K 2K8, Canada  
T: 1 800 363-8340  
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

