NEXTSPEED® Jacks

HUBBELL

Xcelerator Category 6 Jack

Features

- Third Party Verified Category 6 Component Compliant
- Exclusive 1-Punch Termination Reduces Termination Time by 75%
- Mating Cycles Exceed Industry Standard by Four Times
- Bulk Packaging Reduces Excess Waste on the Job

Ordering Information

DescriptionColorCatalog No.UPCNEXTSPEED XceleratorGrayHXJ6GY662620825304Category 6 Component Jack,
1 Jack

Listings

ANSI/TIA/EIA-568-C.2 Category 6 component ISO 11801/60603-7-41 Category 6 component Mechanical: Verified to TIA-568-C.2 UL Listed 1863 Mechanical TIA-568-C.2 CSA Certified RoHS Compliant

Specifications

Nose Contact

Beryllium copper with precious metal plating over nickel under plating

IDC Contact

Phosphor bronze with 100 micro-inch tin lead 60/40 plating over nickel under plating

Housing

High impact thermoplastic (UL 94 V-0)

Stuffer Cap

Lexan® (UL 94 V-0)

Performance

Electrical

Center balanced to Category 6 plug specifications Positive PSACR beyond 300 MHz (channel) 4+Gbs capacity within the bandwidth of 1-250MHz (channel) Qualified to 150% of 802.3bt PoE Current Level

General Information

Backward compatible to lower installed Categories Icon Compatible Supporting 606-B requirements 100% factory tested

Mechanical


Nose Contact Mating Cycles: 2000 IDC Contact Termination: 10x Keystone Latching Force: 25 lbs.

Contact performance confirmed over the full range of ISO/FCC compliant plug

Applications

IEEE 802.3ab 1000GBASE-T IEEE 802.3bt 4PPoE Power over Ethernet TIA TSB-155 10GbE Over 55 Meters





Accessories

 1-Punch Tool
 TX4P

 Category 6 Patch Cord
 HC6GY03

 Dust Cover
 HXJDC25

 Termination Puck
 HXTP25

 Category 6 Cable
 C6SPB

Online Resources

Customer Use Drawing eCatalog

