



BACK-UP ALARMS

CE	R10	UL	IP65	IP66
		SA950 SA951 only	SA950 only	SA920 only

SMART ALARM[®] Surface/Grommet Mount

ECCO's range of Smart Alarms[®] were the world's first self-adjusting back-up alarms. Smart Alarms constantly measure ambient noise and adjust their sound level, creating a volume that is safe without being annoying or contributing to noise pollution. Smart Alarms eliminate the need for constant manual adjustment and help prevent intentional alarm disconnection.

Models

PART NO.	TYPE	VOLTAGE	dB(A)	AMPS
SA951	Smart	12-48	77-97	0.2
SA950	Smart	12-24	82-102	0.4
SA955	Smart	12-24	82-102	0.4
SA920	Smart	12-24	97-112	0.6

Features and Benefits

- Smart Alarm technology adjusts output to 5dB above surrounding noise
- Sealed in epoxy for protection against dust, moisture and vibration
- Reduces irritation and noise complaints
- Eliminates confusion on which alarm to choose
- Temperature range: -40°F to +185°F (-40°C to +85°C)



BACK-UP ALARMS



excluding
SA901N
SA907N
SA940



EA9780
SA901N
SA931N
SA907N
only

EA9724
SA901N
SA931N
SA907N
only

EA9070
only

SMART ALARM[®] Surface/Grommet Mount

ECCO's range of Smart Alarms[®] were the world's first self-adjusting back-up alarms. Smart Alarms constantly measure ambient noise and adjust their sound level, creating a volume that is safe without being annoying or contributing to noise pollution. Smart Alarms eliminate the need for constant manual adjustment and help prevent intentional alarm disconnection.

Features and Benefits

- Smart Alarm technology adjusts output to 5dB above surrounding noise
- Sealed in epoxy for protection against dust, moisture and vibration
- Reduces irritation and noise complaints
- Eliminates confusion on which alarm to choose
- Temperature range: -40°F to +185°F (-40°C to +85°C)

PART NO.	TYPE	VOLTAGE	dB(A)	AMPS
EA9724	Smart, MFA	12-24	77-97	0.4
EA9780	Smart, MFA	36-80	77-97	0.6
SA931N	Smart	12-48	82-102	0.4
SA901N	Smart	12-24	82-107	0.2
SA907N	Smart	12-24	82-107	0.3
EA9070	Smart, MFA	12-24	87-107	0.2
SA914N	Smart, OEM Mounting	12-24	87-112	0.6
SA917N	Smart	12-24	87-112	1.5
SA940	Smart, Grommet	12-24	87-112	0.5