



Cut

This industrial protective sleeve offers best-in-class protection with unmatched comfort

- INTERCEPT™ Seamless High Performance Polyethylene (HPPE) Without thumbslot
- This industrial protective sleeve with INTERCEPT™ Cut Resistance Technology provides best-in-class cut protection and a soft and cool feel to the worker
- The seamless design and the options of lengths and widths ensure an excellent fit and makes it the n°1 choice for all day comfort
- The HyFlex® 11-250 INTERCEPT™ industrial protective sleeves are engineered to perform in combination with any HyFlex® cut resistant glove
- Red and black over edge is to indicate wide (black) and narrow (red) for easy laundry sorting purpose



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication

Applications

- Press shop operations
- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Handling structural and body components
- Inspection, selecting, checking parts
- Glass repair and replacement
- Seizing structural and body parts
- Body Surface checking, marking and touching up
- Adjusting systems and screwing
- Adjusting panels parts components

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-250

The most comfortable sleeve with Intercept technology

Key Features

- HyFlex® 11-250 without thumb slot come in different lengths and widths for optimal fit and comfort to fit every worker in the best possible way. Color-coding will help for easy sorting after laundry
- 11-250 INTERCEPT™ sleeves are made of black yarn and are silicone free for friendly paint and finish process
- The special knitted bicep cuffs keep the sleeve in place
- Compliant with FDA food handling regulations 21 CFR 177.1520 and 21 CFR 177.2600

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
HyFlex® 11-250	Liner Material: Ansell INTERCEPT™ Technology Cuff Style: Knitwrist without thumbslot		Narrow, Wide, Extra Wide	12" (30 cm), 16" (40 cm), 18" (45 cm)	50 sleeves per box

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

