

H201

EASY COUPLE™



Construction:

Tube: Vinyl Nitrile (RMA Class A)

Reinforcement: 1-braid fiber

Cover: (BK) Neoprene (BU,GN,GY,RD,YW) Vinyl nitrile (Red, green and black are MSHA approved)

Application:

- Air and water transfer
- Pneumatic tools
- Air tools

Operating Temperature:

Air and water
-40°C to +100°C
(-40°F to +212°F)

Oil
-40°C to +127°C
(-40°F to +260°F)

Markets:

- Oil and gas exploration
- Construction
- Mining
- Plastic molding

Type of Couplings:

- Aeroquip® socketless
- Push-on couplings
- Eaton "B" series
- Eaton quick disconnect

# Part No.	 Hose I.D.			 Hose O.D.		 Max Operating Pressure		 Burst Pressure		 Weight		 Length	
	DN	mm	in	mm	in	bar	psi	bar	psi	kg/m	lbs/ft	mtr	ft
H20104XX	6	6,4	0.25	12,7	0.50	21,0	300	84,0	1200	0,13	0.09	15,2	50
H20104XX-250R**	6	6,4	0.25	12,7	0.50	21,0	300	84,0	1200	0,13	0.09	76,2	250
H20104XX-500R	6	6,4	0.25	12,7	0.50	21,0	300	84,0	1200	0,13	0.09	152,4	500
H20106XX	10	9,5	0.38	16,7	0.66	21,0	300	84,0	1200	0,19	0.13	15,2	50
H20106XX-250R**	10	9,5	0.38	16,7	0.66	21,0	300	84,0	1200	0,19	0.13	76,2	250
H20106XX-500R	10	9,5	0.38	16,7	0.66	21,0	300	84,0	1200	0,19	0.13	152,4	500
H20108XX	12	12,7	0.50	19,2	0.76	21,0	300	84,0	1200	0,22	0.15	15,2	50
H20108XX-250R**	12	12,7	0.50	19,2	0.76	21,0	300	84,0	1200	0,22	0.15	76,2	250
H20108XX-500R	12	12,7	0.50	19,2	0.76	21,0	300	84,0	1200	0,22	0.15	152,4	500
H20110XX	16	15,9	0.62	23,6	0.93	21,0	300	84,0	1200	0,34	0.23	15,2	50
H20110XX-250R	16	15,9	0.62	23,6	0.93	21,0	300	84,0	1200	0,34	0.23	76,2	250
H20112XX	19	19,0	0.75	26,3	1.04	21,0	300	84,0	1200	0,39	0.26	15,2	50
H20112XX-250R	19	19,0	0.75	26,3	1.04	21,0	300	84,0	1200	0,39	0.26	76,2	250
H20116XX	25	25,4	1.00	34,9	1.38	14,0	200	55,0	800	0,57	0.38	15,2	50
H20116XX-250R	25	25,4	1.00	34,9	1.38	14,0	200	55,0	800	0,57	0.38	76,2	250

* All sizes available in Black, Blue and Red **Green, Gray and Yellow available