

807x CamView IP Pro Series Security Camera Testers

Designed to facilitate the installation and maintenance of surveillance video equipment

Features:

- **8070** IP Pro works with IP and NTSC/PAL cameras
- **8071** IP Pro+ supports H.264 IP cameras, as well as NTSC/PAL and AHD 1.0 and HD-TVI 2.0 analog video cameras up to 2MP
- **8073** IP Pro-D supports H.264 and H.265 IP cameras, as well as NTSC/PAL, AHD 2.0, CVI 3.0, and TVI 3.0 cameras up to 8MP and has a built-in True RMS multimeter
- **8071** and **8073** work with both SD and HD analog NTSC/PAL camera systems

All models:

- Work with or without a network
- Built-in DHCP server allows you to set & Assign IP addresses to cameras, auto-detect IP settings on networks and Ping, Sniff, List Subnet
- POE for IP cameras or 12VDC to analog cameras
- RS485 port for PTZ control of analog PTZ cameras
- PoE and external power for the camera (up to 12V,15W)
- Code Book so you can save usernames and passwords of the cameras you frequently access/maintain
- Ethernet and network tests; capture images, videos, and camera settings so you can create reports
- Check microphone/audio sources and even provide a bright flashlight function
- Both recorded images and video can be transferred to PCs or other devices via the USB port connection
- TDR cable testing and network testing

Ordering Information:

8070	Triplett CamView IP PRO
8071	Triplett CamView IP PRO+
8073	Triplett CamView IP PRO-D
37-71	Battery, LIPO, 3000MAH,
37-73	Replacement POE injector
37-74	Replacement power cord



Flip-out QWERTY keyboard for quick entry of information



Complete with Lanyard, Rechargeable Battery, Tool Bag with Shoulder Strap, POE Power Injector, Network Cable, BNC Cable, RS485 Cable, 12V Power Output Cable, Audio Cable, USB Cable, and Test Leads (8073 only).

CamView IP Pro Series Camera Testers

Designed to facilitate the installation and maintenance of surveillance video equipment

Specifications

ENCODING	8070	8071	8073
SD Analog	X	X	X
AHD 2.0	X	X	X
AHD 3.0			X
HD-CVI 2.0			X
HD-CVI 3.0			X
HD-TVI 2.0		X	X
HD-TVI 3.0			X
IP (ONVIF only)	X	X	X
H.264	X	X	X
H.265			X
FEATURES			
DHCP Server	X	X	X
MJPEG	X	X	X
12VDC Output	X	X	X
POE Output	15W	15W	15W
TDR Testing	Ethernet only	Ethernet only	Ethernet only
Digital Multimeter			x
RS485 PTZ	X	X	X
Digital Zoom	X	X	X
Data Monitor	X	X	X
Analog Video Generator	X	X	X
HD Video Generator			up to 1080P 30fps
Record Snapshot	X	X	X
Record Video	X	X	X
Camera Report	IP only	IP only	IP only
File Export	X	X	X
Keyboard	Full QWERTY	Full QWERTY	Full QWERTY
Flashlight	X	X	X
PHYSICAL FEATURES			
Screen	Backlit 4" 16.7M color TFT	Backlit 4" 16.7M color TFT	Backlit 4" 16.7M color TFT
Resolution	800 x 480	800 x 480	800 x 480
INPUTS			
BNC	X	X	X
RJ45	X	X	X
OUTPUTS			
BNC	X	X	X
RJ45	X	X	X
USB	Mini	Mini	Mini
Dimensions	7.5 x 4.4 x 1.5" (190 x 113 x 37mm)	7.5 x 4.4 x 1.5" (190 x 113 x 37mm)	7.5 x 4.4 x 1.5" (190 x 113 x 37mm)
Weight	3.5lbs (1.6kg)	3.5lbs (1.6kg)	3.5lbs (1.6kg)