

## CAMERAS


**EC2030-WC**
**EC2014-C**
**EC2014-WC**
**EC2027-WC**

	EC2030-WC	EC2014-C	EC2014-WC	EC2027-WC
<b>approvals</b>	FCC, CE, RoHS, IP67,EU-RED	IP69K, FCC, CE, R10, RCM, RoHS	IP69K, FCC, CE, R10, RoHS	IP69K, FCC, CE, R10, RoHS
<b>color</b>	Yes	Yes	Yes	Yes
<b>discharging time</b>	10 hours (continuous on)	-	-	-
<b>charging time</b>	6 hours	-	-	-
<b>power consumption</b>	-	3.0	1.4	1.7
<b>microphone</b>	Yes	Yes	Yes	Yes
<b>day / night light sensor</b>	Yes	Yes	Yes	Yes
<b>dimensions</b>	4.6" x 2.6" x 3.2"	2.87" x 2.99" x 2.60"	2.87" x 2.99" x 2.98"	3.8" x 2.8" x 2.6"
<b>weight</b>	1.38 lbs	0.74 lbs	0.89 lbs	1 lbs
<b>temperature (F°)</b>	-22F to +158F	-22 to +158	-4 to +158	-4 to +158
<b>lens angle</b>	120°	120°	120°	120°
<b>lens size</b>	120m	1/3"	1/3"	1/3"
<b>Infrared LEDs</b>	4	11	11	12
<b>4 pin camera connection</b>	-	Yes*	-	-
<b>operation frequency</b>	2400-2483.5 MHz	-	-	-
<b>standby mode</b>	30 seconds of inactivity	-	-	-
<b>video codec</b>	AVI	-	-	-

## CAMERAS


**C2013B**
**EC2026-C**
**EC2022-C**
**EC2015-C**
**EC2020-C**

	C2013B	EC2026-C	EC2022-C	EC2015-C	EC2020-C
<b>approvals</b>	IP69K, FCC, CE, RoHS	IP69, FCC, CE, RoHS	IP69K, FCC, CE, R10, RCM, RoHS	IP67, FCC, CE, RoHS	IP69, RoHS
<b>color</b>	Yes	Yes	Yes	Yes	Yes
<b>discharging time</b>	-	-	-	-	-
<b>charging time</b>	-	-	-	-	-
<b>power consumption</b>	1.0	1.8	1.3	< 1.0	2.0
<b>microphone</b>	-	-	-	-	-
<b>day / night light sensor</b>	Yes	-	Yes	Yes	-
<b>dimensions</b>	2.92" x 3.01" x 2.62"	7.7" x 1.9" x 1.6"	12.3" x 6.3" x 1.2"	1.69" x 1.24" x 1.1"	0.9" x 0.9" x 0.9"
<b>weight</b>	0.6 lbs	0.16 lbs	0.73 lbs	0.14 lbs	0.11 lbs
<b>temperature (F°)</b>	-22 to +158	-22 to +158	-22 to +158	-22 to +158	-22 to +158
<b>lens angle</b>	120°	170°	150°	120°	170°
<b>lens size</b>	1/4"	3/5"	3/5"	-	3/5"
<b>Infrared LEDs</b>	18	-	4	10	-
<b>4 pin camera connection</b>	Yes*	Yes*	Yes*	Yes*	Yes*
<b>operation frequency</b>	-	-	-	-	-
<b>standby mode</b>	-	-	-	-	-
<b>video codec</b>	-	-	-	-	-