

SMALL SIZE. BIG RESULTS.



FEATURES

- Foot pedal compartment for easy storage
- Built-in Electric cord holder
- Interchangeable cleaning tools
- Quick connect shaft to manifold and shaft to brush
- .5 HP Motor
- Available in 115v 50/60Hz AC or 230v 50/60Hz AC
- Portable, compact design
- Rugged/Durable molded outer shell

I-RAM-EX-100 - Portable and Compact

The new I-RAM-EX-100 is the latest in the line of award-winning tube cleaners. Designed for the ultimate experience in portability, this compact tube cleaner includes all the innovative features you expect and the benefits you demand from a Goodway product. Integrated flush, 860 RPM reversible shaft rotation, quick connect shaft and brushes and all at half the size of our traditional tube cleaners. That's big news.


I-RAM-EX-100:..... Call for Price

	I-RAM-EX-100
Tube Range	7 mm - 25 mm
Motor Power	1/2 hp (0.37 kW)
Input Power	115 V, 50/60 Hz, 9.0 Amps 230 V 50/60 Hz 4.5 Amps
Power Supply Cord	20' 14/3 GFCI
Air Requirement	None
Shaft Speed	860 rpm
Weight	38 lbs
Shaft Length	3.6 m, 5.2 m, 7.6 m, 10.7 m, & 13.7 m (Available Lengths)
Dimensions	55 cm x 42 cm x 23 cm


SHAFTS AND BRUSHES

Flexible Shaft: High performance Nylon coated shaft.

SHAFT	7/16" - 1/2" I.D. TUBES	9/16" - 1" I.D. TUBES
15' (4.5 meters)	SC-TC-S02-15R	SC-TC-S03-15R
25' (7.5 meters)	SC-TC-S02-25R	SC-TC-S03-25R
35' (10.6 meters)	SC-TC-S02-35R	SC-TC-S03-35R



Nylon Brush: 7/16" - 1" ID Tubes. Compact, medium bristle action for soft to medium deposits. Brush size should be ordered 1/16th smaller than tube I.D.



Grit Brush: 7/16" - 1" ID Tubes Compact, heavy bristle action for medium deposits and scale buildup.

GOODWAY®
INNOVATIVE MAINTENANCE SOLUTIONS

Call: 1-800-333-7467
Visit: www.goodway.com

Goodway Technologies Corporation
420 West Avenue, Stamford, CT 06902-6384 U.S.A.
Phone: 203-359-4708 • Fax: 203-359-9601 • distribution@goodway.com