

# PIG® Grippy® Adhesive-Backed Floor Mat

GRP36201 36" x 50', 1 roll

Hassling with rubber-backed floor mats or rental mats? Make the switch to the mat that sticks — our super-safe, adhesive-backed commercial absorbent runner. Perfect for grocery and retail environments.

- Now there's a whole new way to keep your floor safe — PIG Grippy Floor Mat is highly absorbent, very low profile, extremely durable and effortless to maintain
- Adhesive-backed floor mat stays exactly where you put it with no shifting, bunching up or flipping over; traps dirt, salt and moisture to keep it from being tracked around
- Sticks to most commercial floor surfaces including concrete, VCT, linoleum, ceramic tile, quarry tile and laminate flooring
- Proprietary adhesive sticks to the floor with a super-tight grip, but peels up easily
- Extreme durability that stands up to heavy traffic — even forklifts — to keep it on the job for up to 12 weeks
- Easy to use: roll out continuous walk-off coverage for entrances and walkways with no gaps, ripples or overlaps that cause slips and trips
- Easy to clean: you can sweep, vacuum, mop, use your shop/wet vac or run your floor scrubber over Grippy Mat and it won't budge
- Easy to customize: lets you create custom-size floor mats for transition areas and wet problem spots
- Highly efficient absorbent top soaks in moisture, wicks and spreads it evenly so the mat dries out quickly — ideal for entrances and anywhere you need maximum absorbency for water
- 36" x 50' regular mediumweight roll provides enough length to create continuous walk-off runners to stop dirt and moisture at the door
- Available in gray, black and tan to match your surroundings
- Absorbs a wide variety of liquids including water, oil and grease; leakproof backing prevents liquid from soaking through to the floor
- The thinnest commercial floor mat you can buy: no rippled edges to obstruct doors or create tripping hazards. ADA compliant for



- wheelchairs and walkers; carts and pallet jacks roll right over it
- Only a fraction of the weight of rubber-backed mats: no more back strain when you change your mats
- Completely eliminates rental mat hassles and can save up to 50% per year over rental contracts
- PIG Grippy Floor Mat has a 91% lower environmental impact than rental floor mats (Please [email us](#) for a copy of the Life Cycle Assessment report\*.)
- Tested and Certified by the National Floor Safety Institute (NFSI): when used as part of your floor safety program, high-traction surfaces such as PIG Grippy Floor Mat have been proven to reduce slip-and-fall claims by as much as 90%
- Mats take on the properties of absorbed liquids
  - always take proper precautions when handling saturated absorbents
- **VIDEO:** [Click here to watch the Installation Video](#)
- **VIDEO:** [Click here to watch Advanced Installation, Maintenance and Removal Techniques - Grocery Example](#)



Item#	Description	Dimensions	Weight
GRP36201-TN	Tan,	36" W x 50' L	12.6 lbs.
GRP36201-GY	Gray,	36" W x 50' L	12.6 lbs.
GRP36201-BK	Black,	36" W x 50' L	12.6 lbs.

**Metric Equivalent:**

Item#	Description	Dimensions	Weight
GRP36201-TN	Tan,	91.4cm W x 15m L	5.7 kg
GRP36201-GY	Gray,	91.4cm W x 15m L	5.7 kg
GRP36201-BK	Black,	91.4cm W x 15m L	5.7 kg

**Specifications**

<b>Antimicrobial</b>	No
<b>Traffic</b>	Heavy Foot Traffic; Carts & Equipment
<b>Backing Material</b>	Adhesive-Backed

<b>Indoor/Outdoor</b>	Indoor Use
<b>Incinerable</b>	Yes
<b>Flammability Specifications</b>	Flame Resistant - Will melt and self-extinguish
<b>Fluid Absorbed</b>	Water; Grease; Oils
<b>Dimensions</b>	36" W x 50' L
<b>Mat Weight</b>	Mediumweight
<b>Absorbency</b>	Up to 4 gal. per roll
<b>Brand</b>	PIG
<b>Category</b>	Grippy® Floor Mat
<b>Core Diameter</b>	3"
<b>Industry</b>	Grocery/Retail; Restaurant; Institutional Facilities
<b>Perforated</b>	No
<b>Storage Temp Range</b>	Store between 32°F and 120°F
<b>Temperature Limit</b>	Surface temps from 55°F to 120°F
<b>Walking Surface</b>	Absorbent Top
<b>Sold as</b>	1 roll
<b>Weight</b>	12.6 lbs.
<b>New Pig Patent</b>	Pending
<b># per Pallet</b>	28
<b>Composition</b>	Absorbent - Polypropylene Adhesive Backing - Proprietary Adhesive Material
<b>UNSPSC</b>	47131901
<b>UV Resistant</b>	No
<b>Pigalog® Page Number</b>	<a href="#">Page 23</a>

## Metric Equivalent

<b>Absorbency</b>	Up to 15.1 L per roll
<b>Dimensions</b>	91.4cm W x 15m L
<b>Weight</b>	5.7 kg

## Technical Information

### Certifications, Approvals and Ratings

ADA Compliant,NFSI Certified,ANSI B101.1- 2009

### Technical Documents

[PIG Grippy® Floor Mat](#)

[Instructions for PIG Grippy Floor Mat](#)

[Case Study – Market Basket Foods](#)

[Eliminate Rental Mats with PIG Grippy Floor Mat](#)

National Floor Safety Institute (NSFI) Certification

PIG Grippy Floor Mat Savings Worksheet

PIG Grippy Floor Mat ADA Compliance

White paper – Slip & Fall Prevention Secrets

\*Citation for Life Cycle Assessment

FAQ for PIG Grippy Floor Mat

New Pig Adhesive-Backed Mat Notice

PIG® Grippy® Floor Mats

29 CFR 1910.22(a)(2)

## Disclaimers

### Safety Instructions Regarding Flammable Liquids for Flame Resistant Mats

Pig Absorbent Mats are flame resistant in their unused state, but take on the properties of flammable liquids they absorb. Always take proper precautions against potential ignition in handling and disposal of these mats if they have absorbed flammable liquids. For further assistance, please call Technical Services.



**One Pork Avenue • Tipton, PA 16684-0304**

1-855-493-4647 • Fax: 1-800-621-7447 • [newpig.com](http://newpig.com) • [hothogs@newpig.com](mailto:hothogs@newpig.com)