

Available Colors: Burgundy, Brown, Hunter Green, Charcoal/Black, Gray, & Blue.



Specialty



A NoTrax® exclusive: **O**pera™ combines 3 functional mats into 1 mat design

- Zone 1 - A looped non-absorbent yarn to scrape debris and moisture from foot traffic
- Zone 2 - Combines looped scraper yarns with absorbent Decalon® looped pile to begin the drying process
- Zone 3 - Pure Decalon® looped pile to complete the drying function.

Test	Test Description	*Results
ASTM D6540	Accelerated Soiling Method	Based on Visual Inspection 4.5 - Vacuum Rating 5.0 - Rating After Extraction
ASTM D412	Breaking Load/Elongation	189.4 lbs/in <sup>2</sup>
ASTM 5252-98a	Accelerated Wear - 4,000 cycles (Hexapod Tumble Drum Tester)	Appearance: 2.5 Color: 2.5
ASTM D3936-05	Delamination	Exceeds Backing Strength
-	Water Retention	Weight Gain = 79.36% (0.27 gal/yd <sup>2</sup> )
ASTM D1335-05	Tuft Bind of Pile Yarn	11.4 = Superior
CPSC FF 1-70	Surface Flammability of Carpets and Rugs Ignition Characteristics - Finished Textile Floor Covering Material	Pass

\*All testing of NoTrax® floor matting has been performed by an independent testing laboratory.

07/2014

Appearance Rating Key

5	No change
4	Slight change
3	Noticeable change
2	Considerable change
1	Severe change

- Yarns are color coordinated to combine beauty with functionality
- Thickness: 3/8"
- Heavyweight vinyl non-slip backing
- Recommended and approved product as a part of the GreenTRAX program for "Green Cleaning" environments
- Stock Sizes: 3' x 10', 3' x 12', 4' x 10', 4' x 12', 6' x 10', 6' x 12'

