



Cut Abrasion Protection



Medium Duty

Durable ISO C/ANSI A4 cut-resistant gloves offering extended glove life

- **Advanced defenses:** Enriched with Lycra® content, the HyFlex® 11-735's liner also benefits from patented INTERCEPT™ Cut Resistance Technology, for ISO C/ANSI level 4 cut protection
- **Superior durability:** Their palm-dipped PU coating makes for robust PPE gloves with long-lasting resilience, achieving EN level 4 and ANSI level 6 abrasion resistance
- **Lightened comfort:** These HyFlex® gloves' 10G lightweight plaited liner ensures a versatile blend of comfort, flexibility and protection
- **Enhanced grip:** The same polyurethane coating enhances these HyFlex gloves' grip and performance in dry or slightly oily conditions
- **Simplified packaging:** These PU-coated gloves also come in vend pack form, for convenient access in times of need



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical
- Automotive Aftermarket

Applications

- Metalworking & assembly operations
- Assembly & inspection of components
- Assembly and disassembly of equipment
- Seizing structural parts
- Mounting and dismantling
- Fastening components, parts
- Loading and unloading trucks and vehicles
- Handling incoming goods
- Maintenance
- Lock smith

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

11-735

Tough and durable cut protection with a breathable, soft liner

Key Features

- **INTERCEPT[™] Cut Resistance Technology:** Advanced personal protection
- **Palm-dipped PU coating:** Excellent grip and abrasion resistance
- **10G lightweight plaited liner:** Soft, flexible, Lycra[®]-imbued comfort

Performance Standards & Regulatory Compliance

REACH Compliant



Technologies



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex [®] 11-735	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Fiber glass, HPPE, Nylon, Spandex Cuff Style: Knitwrist	10	6, 7, 8, 9, 10	224-269 mm; 8.81-10.59 in	Black	<ul style="list-style-type: none"> • 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
 Riverside Business Park
 Blvd International, 55
 1070 Brussels, Belgium
 T: +32 (0) 2 528 74 00
 F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
 111 Wood Avenue South,
 Suite 210
 Iselin, NJ 08830, USA
 T: +1 800 800 0444
 F: +1 800 800 0445

Australia

Ansell Limited
 Level 3,678 Victoria Street,
 Richmond, Vic, 3121
 Australia
 T: +61 1800 337 041
 F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
 (Malaysia) Sdn Bhd
 Prima 6, Prima Avenue
 Block 3512, Jaijan Teknokrat 6
 T: +603 8310 6688
 F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
 Blvd. Bernardo Quintana No. 7001-C,
 Q7001 Torre II,
 Suites 1304, 1305 y 1306,
 Col. Centro Sur, c.p. 76079
 Queretaro, Qro. Mexico
 T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
 105 Lauder
 Cowansville, QC J2K 2K8
 Canada
 T: +1 800 363 8340
 F: +1 800 267 3551

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

