



BUILT TO STAND THE TEST OF TIME.

For consistent clearing performance that pays off, turn to the Classic Sno-Thro® from Ariens. From the handlebars to the housing, the all-steel Classic is built to stand the test of time. The compact design makes it light and easy to control while interlocking levers allow for effortless, one-handed operation. A steel serrated auger cuts through snow allowing a 12", high-speed impeller to send it flying through a quick turn chute.



EASY TO USE

The compact design makes it light and easy to control.

HIGH-SPEED IMPELLER

A 12-inch, 3-blade high-speed impeller throws 58 tons per hour.

INTERLOCKING LEVERS

Gain the upper hand with interlocking levers that allow for effortless, one-handed operation.

SERRATED AUGER

Cut through the toughest snow in a snap with a steel, serrated auger.

2.5X QUICK-TURN CHUTE

Put powder in its place with a 2.5X Quick-Turn Chute with 205-degree rotation.

ALL-STEEL CONSTRUCTION

From the handlebars to the housing, Classic is built to stand the test of time.









DESIGNATION	CLASSIC 24
MODEL #	920025
STAGE TYPE	Two Stage
ENGINE POWER	208cc (9.5 ft/lbs)
ENGINE BRAND	Ariens AX
STARTING SYSTEM	120V/Recoil
CLEARING WIDTH	24 in (60.1 cm)
HOUSING HEIGHT	20 in (50.8 cm)
THROWING DISTANCE	3ft - 40ft (.9-12.2 m)
CHUTE TURNING RADIUS	205°
CHUTE ROTATION	2.5x Quick Turn
DEFLECTOR CONTROL	Remote
TIRE SIZE	13 in x 4 in (33 x 10 cm)
TIRE TYPE	Snow Tread
STEERING	Pin Lock
DRIVE TYPE	Disc-O-Matic
SPEEDS	6 Forward / 2 Reverse
GEAR CASE	Cast Iron
GEAR CASE WARRANTY	5yr Cons, 1yr Comm
IMPELLER PROFILE	Steel 3 Blade
IMPELLER DIAMETER	12 in (30.5 cm)
AUGER DIAMETER	11 in (27.9 cm)
AUGER TYPE	Steel Serrated
SKID SHOES	Steel Reversible
SCRAPER BAR	Steel Adjustable
PRODUCT WARRANTY	3yr Cons, 90 day Comm
LENGTH	53.8 in (135.4 cm)
WIDTH	26.4 in (67.1 cm)
HEIGHT	44 in (111.8 cm)
WEIGHT	187 lbs (84.8 kg)
FEATURES AT A GLANCE	Remote Deflector, Electric Start, Drift Cutters (optional), One Hand Interlock