



WESTWARD®

Item # 440A57

Set Includes:

## Master Tool Set, SAE/Metric, 204 pieces

Mfg Part #	Description
53YP74	Socket, Steel, Chrome, 5/32 in
53YP75	Socket, Steel, Chrome, 3/16 in
53YP76	Socket, Steel, Chrome, 7/32 in
53YP77	Socket, Steel, Chrome, 1/4 in
53YP78	Socket, Steel, Chrome, 9/32 in
53YP79	Socket, Steel, Chrome, 5/16 in
53YP80	Socket, Steel, Chrome, 11/32 in
53YP81	Socket, Steel, Chrome, 3/8 in
53YP82	Socket, Steel, Chrome, 7/16 in
53YP83	Socket, Steel, Chrome, 1/2 in
53YP85	Socket, Steel, Chrome, 4 mm
53YP86	Socket, Steel, Chrome, 4.5 mm
53YP87	Socket, Steel, Chrome, 5 mm
53YP88	Socket, Steel, Chrome, 5.5 mm
53YP89	Socket, Steel, Chrome, 6 mm
53YP90	Socket, Steel, Chrome, 7 mm
53YP91	Socket, Steel, Chrome, 8 mm
53YP92	Socket, Steel, Chrome, 9 mm
53YP93	Socket, Steel, Chrome, 10 mm
53YP94	Socket, Steel, Chrome, 11 mm
53YP95	Socket, Steel, Chrome, 12 mm
53YP97	Socket, Steel, Chrome, 3/16 in
53YP98	Socket, Steel, Chrome, 7/32 in
53YP99	Socket, Steel, Chrome, 1/4 in
53YR01	Socket, Steel, Chrome, 9/32 in
53YR02	Socket, Steel, Chrome, 5/16 in
53YR03	Socket, Steel, Chrome, 11/32 in
53YR04	Socket, Steel, Chrome, 3/8 in
53YR05	Socket, Steel, Chrome, 7/16 in
53YR06	Socket, Steel, Chrome, 1/2 in

Mfg Part #	Description
53YR22	Socket, Steel, Chrome, 1/4 in
53YR23	Socket, Steel, Chrome, 9/32 in
53YR24	Socket, Steel, Chrome, 5/16 in
53YR25	Socket, Steel, Chrome, 11/32 in
53YR26	Socket, Steel, Chrome, 3/8 in
53YR27	Socket, Steel, Chrome, 7/16 in
53YR28	Socket, Steel, Chrome, 1/2 in
53YR34	Socket, Steel, Chrome, 6 mm
53YR35	Socket, Steel, Chrome, 7 mm
53YR36	Socket, Steel, Chrome, 8 mm
53YR37	Socket, Steel, Chrome, 9 mm
53YR38	Socket, Steel, Chrome, 10 mm
53YR39	Socket, Steel, Chrome, 11 mm
53YR40	Socket, Steel, Chrome, 12 mm
53YR65	Socket, Steel, Chrome, 5/16 in
53YR67	Socket, Steel, Chrome, 3/8 in
53YR68	Socket, Steel, Chrome, 7/16 in
53YR69	Socket, Steel, Chrome, 1/2 in
53YR70	Socket, Steel, Chrome, 9/16 in
53YR71	Socket, Steel, Chrome, 5/8 in
53YR72	Socket, Steel, Chrome, 11/16 in
53YR73	Socket, Steel, Chrome, 3/4 in
53YR74	Socket, Steel, Chrome, 13/16 in
53YR75	Socket, Steel, Chrome, 7/8 in
53YR81	Socket, Steel, Chrome, 9 mm
53YR82	Socket, Steel, Chrome, 10 mm
53YR83	Socket, Steel, Chrome, 11 mm
53YR84	Socket, Steel, Chrome, 12 mm
53YR85	Socket, Steel, Chrome, 13 mm
53YR86	Socket, Steel, Chrome, 14 mm



WESTWARD®

Item # 440A57

Set Includes:

## Master Tool Set, SAE/Metric, 204 pieces

Mfg Part #	Description
53YR87	Socket, Steel, Chrome, 15 mm
53YR88	Socket, Steel, Chrome, 16 mm
53YR89	Socket, Steel, Chrome, 17 mm
53YR90	Socket, Steel, Chrome, 18 mm
53YR91	Socket, Steel, Chrome, 19 mm
53YR92	Socket, Steel, Chrome, 20 mm
53YR93	Socket, Steel, Chrome, 21 mm
53YR94	Socket, Steel, Chrome, 22 mm
53YT01	Socket, Steel, Chrome, 5/16 in
53YT03	Socket, Steel, Chrome, 3/8 in
53YT04	Socket, Steel, Chrome, 7/16 in
53YT05	Socket, Steel, Chrome, 1/2 in
53YT06	Socket, Steel, Chrome, 9/16 in
53YT07	Socket, Steel, Chrome, 5/8 in
53YT08	Socket, Steel, Chrome, 11/16 in
53YT09	Socket, Steel, Chrome, 3/4 in
53YT10	Socket, Steel, Chrome, 13/16 in
53YT11	Socket, Steel, Chrome, 7/8 in
53YT18	Socket, Steel, Chrome, 10 mm
53YT19	Socket, Steel, Chrome, 11 mm
53YT20	Socket, Steel, Chrome, 12 mm
53YT21	Socket, Steel, Chrome, 13 mm
53YT22	Socket, Steel, Chrome, 14 mm
53YT23	Socket, Steel, Chrome, 15 mm
53YT24	Socket, Steel, Chrome, 16 mm
53YT25	Socket, Steel, Chrome, 17 mm
53YT26	Socket, Steel, Chrome, 18 mm
53YT27	Socket, Steel, Chrome, 19 mm
53YT73	Socket, Steel, Chrome, 3/8 in
53YT74	Socket, Steel, Chrome, 7/16 in

Mfg Part #	Description
53YT75	Socket, Steel, Chrome, 1/2 in
53YT76	Socket, Steel, Chrome, 9/16 in
53YT77	Socket, Steel, Chrome, 5/8 in
53YT78	Socket, Steel, Chrome, 11/16 in
53YT79	Socket, Steel, Chrome, 3/4 in
53YT80	Socket, Steel, Chrome, 13/16 in
53YT88	Socket, Steel, Chrome, 10 mm
53YT89	Socket, Steel, Chrome, 11 mm
53YT90	Socket, Steel, Chrome, 12 mm
53YT91	Socket, Steel, Chrome, 13 mm
53YT92	Socket, Steel, Chrome, 14 mm
53YT93	Socket, Steel, Chrome, 15 mm
53YT94	Socket, Steel, Chrome, 16 mm
53YT95	Socket, Steel, Chrome, 17 mm
53YT96	Socket, Steel, Chrome, 18 mm
53YT97	Socket, Steel, Chrome, 19 mm
53YU46	Socket, Steel, Chrome, 1/2 in
53YU47	Socket, Steel, Chrome, 9/16 in
53YU48	Socket, Steel, Chrome, 5/8 in
53YU49	Socket, Steel, Chrome, 11/16 in
53YU50	Socket, Steel, Chrome, 3/4 in
53YU51	Socket, Steel, Chrome, 13/16 in
53YU52	Socket, Steel, Chrome, 7/8 in
53YU53	Socket, Steel, Chrome, 15/16 in
53YU54	Socket, Steel, Chrome, 1 in
53YU55	Socket, Steel, Chrome, 1 1/16 in
53YU56	Socket, Steel, Chrome, 1 1/8 in
53YU57	Socket, Steel, Chrome, 1 3/16 in
53YU58	Socket, Steel, Chrome, 1 1/4 in
53YU61	Socket, Steel, Chrome, 10 mm



WESTWARD®

Item # 440A57

Set Includes:

Master Tool Set, SAE/Metric, 204 pieces

Mfg Part #	Description
53YU62	Socket, Steel, Chrome, 11 mm
53YU63	Socket, Steel, Chrome, 12 mm
53YU64	Socket, Steel, Chrome, 13 mm
53YU65	Socket, Steel, Chrome, 14 mm
53YU66	Socket, Steel, Chrome, 15 mm
53YU67	Socket, Steel, Chrome, 16 mm
53YU68	Socket, Steel, Chrome, 17 mm
53YU69	Socket, Steel, Chrome, 18 mm
53YU70	Socket, Steel, Chrome, 19 mm
54PR23	Spark Plug Socket, 5/8 in, Steel
54PR24	Spark Plug Socket, 13/16 in, Steel
54PR16	Skt Adptr, Steel, Chrome, 3/8 in Output
53YV66	Socket Extension, Chrome, Drv 1/4 in
53YV69	Socket Extension, Chrome, Drv 3/8 in
53YV72	Socket Extension, Chrome, Drv 1/2 in
53YV76	Hand Ratchet, 5 in, Chrome, 1/4 in
53YV77	Hand Ratchet, 8 1/4 in, Chrome, 3/8 in
53YV78	Hand Ratchet, 11 in, Chrome, 1/2 in
54TN08	Socket Bit, Steel, 1/4 in, TpSz T10
54TL56	Socket Bit, Steel, 3/8 in, TpSz 1/8 in
54TL57	Socket Bit, Steel, 3/8 in, TpSz 5/32 in
53YV79	Socket Bit, Steel, 3/8 in, TpSz 3/16 in
53YV80	Socket Bit, Steel, 3/8 in, TpSz 7/32 in
53YV81	Socket Bit, Steel, 3/8 in, TpSz 1/4 in
53YV82	Socket Bit, Steel, 3/8 in, TpSz 5/16 in
53YV83	Socket Bit, Steel, 3/8 in, TpSz 3/8 in
54TL58	Socket Bit, Steel, 3/8 in, TpSz 4 mm
54TL59	Socket Bit, Steel, 3/8 in, TpSz 5 mm
54TL60	Socket Bit, Steel, 3/8 in, TpSz 6 mm
54TL61	Socket Bit, Steel, 3/8 in, TpSz 7 mm

Mfg Part #	Description
54TL62	Socket Bit, Steel, 3/8 in, TpSz 8 mm
54TL76	Socket Bit, Steel, 3/8 in, TpSz 9 mm
54TL63	Socket Bit, Steel, 3/8 in, TpSz 10 mm
53YV84	Socket Bit, Steel, 3/8 in, TpSz T15
53YV85	Socket Bit, Steel, 3/8 in, TpSz T20
53YV86	Socket Bit, Steel, 3/8 in, TpSz T25
53YV87	Socket Bit, Steel, 3/8 in, TpSz T27
53YV88	Socket Bit, Steel, 3/8 in, TpSz T30
53YV89	Socket Bit, Steel, 3/8 in, TpSz T40
53YV90	Socket Bit, Steel, 3/8 in, TpSz T45
53YV92	Socket Bit, Steel, 3/8 in, TpSz #1
53YV93	Socket Bit, Steel, 3/8 in, TpSz #2
53YV94	Socket Bit, Steel, 3/8 in, TpSz #3
53YV75	Socket Extension, Chrome, Drv 1/2 in
53YV95	Socket Bit, Steel, 3/8 in, TpSz 3/16 in
53YV96	Socket Bit, Steel, 3/8 in, TpSz 1/4 in
54TN54	Socket Bit, Steel, 1/2 in, TpSz T50
54TN55	Socket Bit, Steel, 1/2 in, TpSz T55
36A207	Combo Wrench, SAE, Rounded, 5/16"
36A208	Combo Wrench, SAE, Rounded, 3/8"
36A209	Combo Wrench, SAE, Rounded, 7/16"
36A210	Combo Wrench, SAE, Rounded, 1/2"
36A211	Combo Wrench, SAE, Rounded, 9/16"
36A213	Combo Wrench, SAE, Rounded, 11/16"
36A214	Combo Wrench, SAE, Rounded, 3/4"
36A215	Combo Wrench, SAE, Rounded, 13/16"
36A216	Combo Wrench, SAE, Rounded, 7/8"
36A217	Combo Wrench, SAE, Rounded, 15/16"