

PIG® Burpless® Large Poly Drum Funnel

DRM138 For 30 and 55 gal. Steel Drums w/ 2" NPT, 22" x 11.5"

Economical Burpless Poly Funnel chugs as fast as you can pour, without burps or splashbacks!

- Burpless design vents during pouring for fast, smooth flow with no dangerous splashback
- Lets you pour without venting through 3/4" bung
- Thick-wall, 100% polyethylene construction resists UV rays, rust, corrosion and most chemicals
- Lockable to prevent unauthorized access
- Multiple lid color options let you segregate drums
- Attached hinged lid won't get lost or separated from funnel
- Ridged interior creates a level draining surface for containers and enables faster draining
- Built-in debris strainer captures large particles; add a fine mesh screen (sold separately) to capture small debris
- Threaded brass neck fits 2" NPT bung opening, and funnel can be used on any steel drum or IBC



| Item# | Description | Dimensions | Weight |
|-----------|-------------|-------------------------|------------|
| DRM138-YW | Yellow, | ext. dia. 22" x 11.5" H | 8.115 lbs. |
| DRM138-RD | Red, | ext. dia. 22" x 11.5" H | 8.115 lbs. |
| DRM138-BK | Black, | ext. dia. 22" x 11.5" H | 8.115 lbs. |

Metric Equivalent:

| Item# | Description | Dimensions | Weight |
|-----------|-------------|-----------------------------|--------|
| DRM138-YW | Yellow, | ext. dia. 55.9cm x 29.2cm H | 3.7 kg |
| DRM138-RD | Red, | ext. dia. 55.9cm x 29.2cm H | 3.7 kg |
| DRM138-BK | Black, | ext. dia. 55.9cm x 29.2cm H | 3.7 kg |

Specifications

| | |
|-------------------------|--------------------------------------|
| Drum Lid Closure | Tight-Head |
| Special Feature | Burpless; Padlockable |
| Use With | 30 and 55 gal. Steel Drums w/ 2" NPT |

| | |
|------------------------------------|--|
| Dimensions | ext. dia. 22" x 11.5" H |
| Drum Bung Opening | 2" NPT |
| Drum Size | 30 gal.; 55 gal. |
| Drainage Space | 4.75" H x 17.75" Dia. Draining Area |
| Drum Type | Steel |
| Flame Arrestor Included | No |
| Lid | With Hinged Lid |
| Overfill Preventer Included | No |
| Sold as | 1 each |
| Weight | 8.115 lbs. |
| # per Pallet | 20 |
| Composition | Funnel - Polyethylene Threaded Insert - Brass |
| UNSPSC | 27112902 |
| Pigalog® Page Number | Page 313 |

Metric Equivalent

| | |
|-------------------|-----------------------------|
| Dimensions | ext. dia. 55.9cm x 29.2cm H |
| Weight | 3.7 kg |

Technical Information

Technical Documents

[LDPE Products](#)

Disclaimers

[Flammables Warning](#)

Not for use with flammables (f.p.<141°F/60.5°C).



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com