

XLERATOReco[®] HAND DRYER



ENHANCED STANDARD FEATURES



Adjustable Speed and
Sound Control



Multi-Voltage Options:
110-120V Or 208-277V



500 Watts
No Heat



Externally Visible
Service LED

10
SECONDS¹
dry time

95%
COST SAVINGS
versus paper towels

1.7
WATT HOURS
energy use



XLERATOR^{eco}® HAND DRYER



MODELS: **XL - BW W GR C SB SI SP - ECO -H** (HEPA Filter) OPTIONS: **-1.1N** (Noise Reduction Nozzle) **-VOLTAGE** (See Chart)



XL-BW-ECO
White Thermoset Resin (BMC)

TESTED TO **PCR** DRY TIME: 10 SECONDS' ENERGY PER USE: 1.7 Wh'
GUIDELINES



UL Environment published the first global Product Category Rules (PCR) for hand dryers which outlined industry consensus testing procedures to quantify environmental impact and performance. Third-party testing to these guidelines documents a product's environmental impact over its lifecycle. This impact is detailed in certified, internationally-recognized Environmental Product Declarations (EPDs). EPDs enable specifiers and buyers to make true apples-to-apples comparisons and more informed product selections. Excel Dryer received the industry's first certified EPDs.

FEATURES & BENEFITS

- ✓ **HEPA Filtration System:** Removes 99.999% of viruses² and 99.97% of potentially present bacteria³ at 0.3 microns from the airstream.
- ✓ 50% Longer Life
- ✓ Industry Leading 7-Year Limited Warranty
- ✓ 95% Cost Savings Vs. Paper Towels
- ✓ Helps Qualify For The Most LEED® Credits
- ✓ No Heat Technology
- ✓ Made In USA Certified®
- ✓ A Hygienic Hand Drying Solution
- ✓ Washable Pre-Filter

OPTIONS

- ✓ **1.1" Noise Reduction Nozzle:** Reduces the sound level by 9 decibels by significantly decreasing air deflection noise while only increasing dry time by approximately 3 seconds.



XL-W-ECO
White Epoxy Painted



XL-GR-ECO
Graphite Textured Painted



XL-SP-ECO⁴
Custom Special Paint



XL-SI-ECO⁵
Custom Special Image



XL-C-ECO
Chrome Plated



XL-SB-ECO
Brushed Stainless Steel

PERFORMANCE

ADJUSTABLE SOUND LEVEL: 65-75 dB **ADJUSTABLE VELOCITY:** 13,000-20,000 LFM
FLOW RATE: 43-65 CFM

DIMENSIONS

Width 11 3/4" (298 mm) **Height** 12 11/16" (322 mm) **Depth** 6 11/16" (170 mm)

ELECTRICAL

VOLTS	AMPS	WATTS	HERTZ	
110-120V	4.3-4.5A	460-530W	50/60 Hz	
208-277V	2-2.2A	425-500W	50/60 Hz	
230V	2.2A	500W	50 Hz	

NOTE: Drawing 4.5 Amps or less allows for the installation of multiple XLERATOReco units on one circuit, significantly reducing installation costs and creating a return on investment of less than one year.

CERTIFICATIONS



WEIGHT

XL-BW-ECO: 15 lbs. (6.8 kgs.) **XL-SB-ECO:** 16 lbs. (7.26 kgs.)
XL-W-ECO, XL-GR-ECO, XL-C-ECO, XL-SI-ECO, XL-SP-ECO: 17 lbs. (7.71 kgs.)

ACTIVATION

Automatic Sensor Operated

MOUNTING

Surface Mounted

SUGGESTED MOUNTING HEIGHTS

Men 45" (114 cm) **Women** 43" (109 cm) **Accessible** 37" (94 cm)

Note: Heights measured from floor to bottom of dryer.

ACCESSORIES

- ✓ Antimicrobial Wall Guards (#89B, #89W, #89S)
- ✓ XChanger® Paper Towel Dispenser Retrofit Kit (#40575, #40550)
- ✓ ADA-Compliant Recess Kit (#40502)



¹Dry time and energy use testing performed by SGS International on standard XLERATOR Hand Dryer with 0.8" nozzle to 0.25g or less of residual moisture, pursuant to the UL Environment Global Product Category Rules (PCR) for Hand Dryers. ²Based on testing performed by LMS Technologies, 2020. ³LMS Technologies, 2014. ⁴Special Paint powder-coated covers are available in many colors and textures. ⁵Exclusive digital image technology allows for the addition of company, school or team logos with any color, design or a "green message".



TIME TO THROW IN THE TOWEL®

EXCEL DRYER INC • 1.800.255.9235 • EXCELDRYER.COM

APR 2022

22EDS1088