Pivoting-head luminaire SLJ 500/750/S

113259000-00641174



fitted with

connected load power consumption luminous flux luminous efficacy light distribution light color color rendering index (CRI) glare-free system of protection class of protection technology usage luminaire body lamp cover balance of articulation joints weight (net) mains lead fastening special features

LED

22-26 V; DC approx. 5 W approx. 460 lm approx. 92 lm/W direct, wide-angled beam neutral white, approx. 5000 K >70 screen IP 67 III switchable external aluminium, painted, black glass screen friction approx. 0.9 kg (2.0 lbs) approx. 3 m (9.8 ft); with free stranded wires screw-down flange Flood with 30° angle of radiation

Waldmann W

ENGINEER OF LIGHT.

CE



illuminance



luminous intensity



dimensions in mm

Errors and technical changes excepted. Images can vary from original. Photometric and electrical data may vary due to component tolerances.