Flexible-tube luminaire SLF 500/750/S

113260000-00641130



fitted with

connected load power consumption luminous flux luminous efficacy light distribution light color color rendering index (CRI) glare-free system of protection class of protection technology usage luminaire body lamp cover tubular sections weight (net) mains lead fastening special features

LED

22-26 V: DC approx. 5 W approx. 490 lm approx. 98 lm/W direct, narrow-angled beam neutral white, approx. 5000 K >70 screen IP 67 Ш switchable pressure switch aluminium, painted, black glass screen flexible metal tube, black approx. 1.6 kg (3.5 lbs) approx. 3 m (9.8 ft); with free stranded wires screw-down flange Spot with a 10° angle of radiation

ENGINEER OF LIGHT.

Waldmann W

CE



illuminance



luminous intensity

10





