

ENGINEER OF LIGHT.



fitted with

work equipment connected load power consumption luminous flux luminous efficacy light color color rendering index (CRI) glare-free system of protection class of protection technology usage luminaire body lamp cover weight (net) mains supply

design fastening dimension special features

## LED

electronic driver 120-240V: 50/60Hz approx. 37 W approx. 3000 lm approx. 81 lm/W neutral white, approx. 5000 K > 80 structured screen IP 20 T switchable rocker switch aluminium/plastic, anodized, aluminium colored anodized structured screen approx. 3.2 kg (7.05 lbs) connection box, built-in plug GST 18i3F REV mounted version screw down lash A=899 mm (35.39") through-wired





GST 18i3F REV





105

90' 75'

60

45



measurements in mm



Errors and technical changes excepted. Images can vary from original. Photometric and electrical data may vary due to component tolerances.