

BATTERY BACKPACK VACUUM



Product Specifications

FEATURES	SPECIFICATIONS
Product Name	Aspen™ 6B
TECHNICAL REQUIREMENTS	
Vacuum Motor	
Vac Motor Power	408 W
Vac Motor Current	11.35 amps
Vac Motor Airflow	70 CFM / 118 m ³ /m
Vac Motor Sealed Water Lift	65 in / 165 mm
Vac Motor Thermal Protection	Thermal protector w/ auto reset
Filtration	
HEPA Filter, Standard	99.97% @ 0.3 micron
Vacuum Bag	
Vacuum Bag	Paper bag is standard
Easy to Change Vac Bag	Two over-center latches
Vacuum Capacity	6 qt / 5.7 L
Body / Frame	
Harness	Deuter® with 27-54 in / 686-1372 mm adjustability
Weight	19.0 lbs / 8.6 kg (9.75 lbs / 4.4 kg body, 3.5 lbs / 1.59 kg harness, 5.75 lbs / 2.6 kg battery)
Dimensions	H: 21 in / 533 mm (25 in / 635 mm with harness) W: 9.5 in / 241 mm (11 in / 279 mm with harness) D: 7 in / 178 mm (10 in / 254 mm with harness)
Electrical / Power	
Power Source	36 v DC / 10.4 Ah lithium ion battery
Interchangeable battery pack	Yes
Run time	Up to 55 minutes
Charge time	2.5 hours
On/Off Switch	Switch is part of battery frame located on the back right
Vacuum Hose	
Hose Length	2-6 ft / 0.61-1.80 m Stretch hose Included with vacuum
Hose Diameter @ wand	1.50 in / 38 mm

Product Specifications (continued)

FEATURES	SPECIFICATIONS
Product Name	Aspen™ 6B
TECHNICAL REQUIREMENTS (cont.)	
Wand & Tools	
Base Kit	<ul style="list-style-type: none"> - Two piece locking S-wand, Aluminum - 14 in / 356 mm carpet tool w/bumper - 14 in / 356 mm nylon fill floor brush - 1.50 in / 38 mm components
Standard Kit	<ul style="list-style-type: none"> - Chrome telescopic S-wand - 14 in / 356 mm carpet tool w/bumper - 14 in / 356 mm nylon fill floor brush - 1.50 in / 38 mm components
Premium Kit	<ul style="list-style-type: none"> - Two piece 59 in / 1499 mm anodized aluminum wand - 18 in / 457 mm Sidewinder® carpet tool - 18 in / 457 mm Sidewinder® nylon floor brush - 1.50 in / 38 mm components
Anti-static machine	Anti-static performance
Max CRI Rating*	TBD
Sound Level	
Sound pressure test (per IEC-60335-2-69 section EE.2.1)	63 dBA
REGULATORY / SAFETY	
US & Canada (ETL listed**)	Yes
AFTERMARKET PARTS	
Kit, Harness hip extension	Enable extension length to 72 in / 1829 mm
Tool Accessory Kit	<ul style="list-style-type: none"> - 5 in / 127 mm natural fill dusting tool - 5 in / 127 mm upholstery tool - 15 in / 381 mm crevice tool - 1.50 in / 38 mm components

* See CRI website for qualified tools for all competitors

** Tested to the UL standard

Specifications are subject to change without notice

Deuter® is a registered trademark of Deuter Sport GMBH

Sidewinder® is a registered trademark of JanPro Products