



**MCR
SAFETY**

FG305

Flex Tuff

Dipped

Specification Sheet

PRODUCT DESCRIPTION:

Our top selling FlexTuff® styles are manufactured on seamless knit liners that are flat dipped to reproduce the natural curved shape of the hand. As a result, workers benefit from less hand fatigue and greater productivity while performing detailed tasks to heavy duty jobs. The FG305 features a 10 gauge cotton/polyester white shell with a blue latex coating over the knuckle.

FEATURES:

- Natural rubber provides abrasion resistance
- Greatly improves grip
- Excellent comfort and fit
- Textured palm

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Material Handling



TECHNICAL DATA FOR: FG305

Series	Flex Tuff
Material Group	Strings
Product Type	Dipped
Glove Size	Large
Gauge	10 Gauge
Material	Cotton Polyester Blend

EN 388 : CE Score - Abrasion	3
EN 388 : CE Score - Cut	1
EN 388 : CE Score - Tear	4
EN 388 : CE Score - Puncture	3
ANSI Abrasion	ANSI Abrasion 4

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

FG305

Flex Tuff

Dipped

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
FG305L	Large	10.040	5.560	3.540	36.876 lb.	3.073
FG305M	Medium	9.370	5.32	3.15	35.256 lb.	2.938
FG305S	Small	8.66	4.72	2.95	29.340 lb.	2.445
FG305XL	X - Large	10.700	5.830	3.620	43.596 lb.	3.633

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved