



**MCR
SAFETY**

CP14 MCR Guard Unsupported Specification Sheet

PRODUCT DESCRIPTION:

MCR Guard has been battle tested in conflicts around the world and offers excellent permeation resistance to most acids, aldehydes, alcohols, amides, bases, esters, and ketones. These gloves are produced domestically with a unique solution dipped process. No other process can achieve such a tight molecular structure, the key to chemical impermeability. MCR Guard is made with the finest Butyl rubber for outstanding protection. The CP14 is a 14 mil smooth finish glove that features a rolled cuff and is 14 inches in length for added protection.

FEATURES:

- Excellent Chemical Resistance
- 14 inch Gauntlet
- 14 mil smooth finish
- Component materials comply with all relevant federal regulations for food contact

APPLICATIONS:

First responder, Biological Hazards, HazMat, Laboratory Technician, Petrochemical industries, Aerospace, Agriculture, Biomedical



TECHNICAL DATA FOR: CP14

Series	MCR Guard	Overall Length	14 in.
Material Group	Unsupported		
Product Type	Unsupported		
Glove Size	Large		
Material	Butyl		
Grade	Industrial Grade		
Features	Sold by pair		
Lining	Unlined		
Thumb Style	Wing		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

CP14

MCR Guard

Unsupported

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
CP14L	Large	14.5	5.63	N/A	22.320 lb.	0.310
CP14M	Medium	14.00	5.13	N/A	18.720 lb.	0.260
CP14S	Small	14.00	4.88	N/A	18.936 lb.	0.263
CP14XL	X - Large	14.5	6.01	N/A	22.392 lb.	0.311

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved