



**MCR
SAFETY**

CP14R MCR Guard Unsupported Specification Sheet

PRODUCT DESCRIPTION:

MCR Guard has been battle tested in conflicts around the world and offers excellent permeation resistance to most acids, aldehydes, alcohols, amides, bases, esters, and ketones. These gloves are produced domestically with a unique solution dipped process. No other process can achieve such a tight molecular structure, the key to chemical impermeability. MCR Guard is made with the finest Butyl rubber for outstanding protection. The CP14R is a 14 mil textured finish glove that features a rolled cuff and is 14 inches in length for added protection.

FEATURES:

- Excellent Chemical Resistance
- 14 inch Gauntlet
- 14 mil textured finish
- Component materials comply with all relevant federal regulations for food contact

APPLICATIONS:

First responder, Laboratory Technician, Aerospace, Agriculture, Biomedical, Food, HazMat



TECHNICAL DATA FOR: CP14R

Series	MCR Guard	Overall Length	14 in.
Material Group	Unsupported		
Product Type	Unsupported		
Glove Size	Large		
Material	Butyl		
Grade	Industrial Grade		
Features	Sold by pair		
Lining	Unlined		
Thumb Style	Wing		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

CP14R

MCR Guard

Unsupported

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
CP14RL	Large	14.250	5.63	N/A	23.976 lb.	0.333
CP14RM	Medium	13.500	5.13	N/A	21.024 lb.	0.292
CP14RS	Small	13.750	4.88	N/A	21.456 lb.	0.149
CP14RXL	X - Large	14.500	6.01	N/A	16.272 lb.	0.226

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved