



MCR
SAFETY

9679

Memphis

Dipped

Specification Sheet

PRODUCT DESCRIPTION:

These styles are well suited for Multi-Industrial applications that require high dexterity and comfort. The 9679 features 13 gauge nylon with gray flat nitrile palm and fingers.

FEATURES:

- 13 Gauge White Nylon Shell
- Flat Nitrile Coated Palm and Fingers
- CE Score 4121
- Color coded hem to identify sizes

APPLICATIONS:

Agriculture, Assembly Line Production, Automotive Assembly, Construction, Landscaping, Manufacturing, Warehousing



TECHNICAL DATA FOR: 9679

Series	Memphis	EN 388 : CE Score - Abrasion	4
Material Group	Strings	EN 388 : CE Score - Cut	1
Product Type	Dipped	EN 388 : CE Score - Tear	2
Glove Size	Large	EN 388 : CE Score - Puncture	1
Gauge	13 Gauge		
Material	Nylon		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

9679
Memphis
Dipped
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9679L	Large	10.35	5.1	2.75	16.476 lb.	1.373
9679M	Medium	9.95	5.1	2.75	15.468 lb.	1.289
9679S	Small	9.45	4.7	2.5	13.812 lb.	1.151
9679XL	X - Large	10.95	5.5	2.95	17.904 lb.	1.492
9679XS	X - Small	9.15	4.7	2.5	12.264 lb.	1.022

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved