



**MCR
SAFETY**

5300

**Unsupported
Specification Sheet**

PRODUCT DESCRIPTION:

These durable nitrile gloves contain no latex proteins and offer excellent resistance to punctures and tears. Nitrile gloves are three times more puncture resistant than rubber and can be used to offer superior resistance to many types of chemicals. This glove is an excellent alternative for individuals who experience allergic reactions to latex.

FEATURES:

- 8 mil, Blue unlined nitrile
- Component materials comply with all federal regulations for food contact
- 12" length
- Straight Cuff

APPLICATIONS:

Canning, Dairy, Poultry processing, Cafeteria, Laboratory Technician, Janitorial , Bottling, Food



TECHNICAL DATA FOR: 5300

Material Group	Unsupported	Overall Length	12 in.
Product Type	Unsupported	EN 388 : CE Score - Abrasion	2
Glove Size	Large	EN 388 : CE Score - Cut	X
Material	Nitrile	EN 388 : CE Score - Tear	X
Grade	Industrial Grade	EN 388 : CE Score - Puncture	1
Lining	Unlined	FDA Accepted Materials	FDA Compliant
Thumb Style	Straight		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

5300

Unsupported
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
5300L	Large	13.00	5.48	N/A	14.028 lb.	1.169
5300M	Medium	13.00	5.24	N/A	13.404 lb.	1.117
5300S	Small	13.00	4.76	N/A	12.900 lb.	1.075
5300XL	X - Large	13.0	5.87	N/A	15.408 lb.	1.284

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved