



**MCR
SAFETY**

5319E

Nitri-Chem

Unsupported Specification Sheet

PRODUCT DESCRIPTION:

Nitrile gloves are three times more puncture resistant than rubber and can be used to offer superior resistance to many types of chemicals. This glove is an excellent alternative for individuals who experience allergic reactions to latex. The 5319E series features include: 13" length, flock lined, 15 mil, straight cuff, and diamond grip.

European Sizes: 5317E = M, 5318E = L, 5319E = XL, 5320E = XXL, 5321E = XXXL

Click on size links below for size specific specifications.



FEATURES:

- 15 Mil Green Nitrile
- Flock Lined
- Raised Diamond Grip
- 13 Inch Length
- Straight Cuff
- Component materials comply with all relevant federal regulations for food contact

APPLICATIONS:

Bottling, Canning, Dairy, Painting, Beef processing, Food

TECHNICAL DATA FOR: 5319E

Series	Nitri-Chem	Overall Length	13 in.
Material Group	Unsupported	EN 388 : CE Score - Abrasion	4
Product Type	Unsupported	EN 388 : CE Score - Cut	1
Glove Size	Large	EN 388 : CE Score - Tear	1
Material	Nitrile	EN 388 : CE Score - Puncture	X
Grade	Economy Grade		
Lining	Flocked		
Thumb Style	Straight		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

5319E
Nitri-Chem
Unsupported
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
5319E	Large	12.40	5.48	N/A	23.316 lb.	1.943
5318E	Medium	12.40	5.24	N/A	22.584 lb.	1.882
5317E	Small	12.40	4.76	N/A	21.720 lb.	1.810
5320E	X - Large	12.40	5.87	N/A	24.504 lb.	2.042
5321E	XX - Large	12.40	6.28	N/A	27.132 lb.	2.261