



**MCR  
SAFETY**

# 6514SJ

## Supported / Dipped gloves Specification Sheet

### PRODUCT DESCRIPTION:

Best bang for your buck. PVC offers unmatched performance at an affordable cost. Double dipped PVC coated gloves provide excellent protection. Glove lengths from knit wrist to 18" provide different levels of protection. The 6514SJ is a 14 inch industry standard black double dipped glove that features a textured finish, jersey lining, and gauntlet cuff.

### FEATURES:

- PVC
- Black Double Dipped
- Jersey Lined
- Textured Finish
- 14

### APPLICATIONS:

Food, Fisheries



### TECHNICAL DATA FOR: 6514SJ

<b>Material Group</b>	Supported	<b>Overall Length</b>	14 in.
<b>Product Type</b>	Supported / Dipped gloves		
<b>Glove Size</b>	Large		
<b>Material</b>	PVC		
<b>Grade</b>	Industrial Grade		
<b>Lining</b>	Jersey		
<b>Thumb Style</b>	Wing		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved



**MCR**  
SAFETY

# 6514SJ

Supported / Dipped gloves  
Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
6514SJ	Large	14.000	6.09	N/A	41.046 lb.	6.841

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: [www.mcrcsafety.com](http://www.mcrcsafety.com)

©2018 MCR Safety - All Rights Reserved