



**MCR
SAFETY**

6421

Memphis PVC

**Supported / Dipped gloves
Specification Sheet**

PRODUCT DESCRIPTION:

Best bang for your buck. PVC offers unmatched performance at an affordable cost. Double dipped PVC coated gloves provide excellent protection. Glove lengths from knit wrist to 18" provide different levels of protection. The 6421 is an industry standard green double dipped, sandy finish, jersey lined glove with a gauntlet cuff. Glove is 10" in length.

FEATURES:

- 10 inches
- PVC
- Double Dipped
- Hunter Green

APPLICATIONS:

Agriculture, Farming, Janitorial , Landscaping, Material Handling, Petrochemical industries, Sanitation



TECHNICAL DATA FOR: 6421

Series	Memphis PVC
Material Group	Supported
Product Type	Supported / Dipped gloves
Glove Size	Large
Material	PVC
Grade	Industrial Grade
Lining	Jersey
Thumb Style	Wing

Overall Length 10 in.

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

6421

Memphis PVC

Supported / Dipped gloves

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
6421	Large	10.000	6.09	N/A	26.748 lb.	4.458

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved