

Previously known as: MICROCHEM® by AlphaTec® 3000 - Model 122

## Durable material providing an effective barrier against a range of inorganic chemicals and biological agents.

- Multi-layer barrier fabric provides effective protection against numerous chemicals
- Designed to protect, typical innovative features include dual zip systems and double cuffs
- Lightweight and durable
- Highly visible bright yellow color for improved worker safety
- Anti-static, tested according to EN 1149-5

### Industries

- Chemical
- Mining
- Oil and gas
- Life Sciences
- Food Processing

### Applications

- Transferring liquids and solids between vessels and tanks and process equipment
- Unexpected leakages spills or other releases
- Opening and draining pumps valves or lines
- Loading and unloading trucks and vehicles
- Filling, blending and charging of raw materials
- Product inspection
- Mixing or loading chemicals
- Cleaning of plant and machines



# AlphaTec®

ADVANCED CHEMICAL PROTECTION

## 3000 - Model 122

Durable, comfortable multi-layer chemical barrier, Type 3/4/5 protection

Previously known as: MICROCHEM® by AlphaTec® 3000 - Model 122

### PRODUCT INFORMATION

<b>Product Material</b>	Multi-layer non woven barrier laminate fabric
<b>Design Features</b>	Coverall with 2-piece hood, double zip closure, elasticated hood, waist & sleeve over cuffs and integrated socks with boot overflap.
<b>Seam Type</b>	Ultrasonically Welded Seams
<b>Standards Overview</b>	CE CATEGORY III (Type 3-B, Type 4-B, Type 5-B, EN 1073-2, EN 14126, EN 1149-5)
<b>Product Reference</b>	3000 - Model 122
<b>Sizes</b>	S-3XL (02-07)
<b>Weight</b>	80gsm

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: [www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.