

Previously known as: MICROCHEM[®] by AlphaTec[®] 5000 - Model 122

Engineered to protect with excellent protection and durability against a wide range of chemical hazards.

- Outstanding permeation performance to numerous organic and inorganic chemicals, biological hazards and chemical warfare agents
- Exceptional barrier protection, providing >480 minutes breakthrough time against 14 of 15 chemicals listed in EN ISO 6529
- Highly visible bright orange colour for improved worker safety
- Welded and taped seams, our highest barrier to liquids and particulates
- Designed to protect, typical innovative features include dual zip systems, double cuffs with knitted inner cuffs
- Multi-layer barrier material which is lightweight, yet strong and durable
- Anti-static, tested according to EN 1149-5

Industries

- Chemical
- Life Sciences
- Mining
- Fire and Rescue
- Oil and gas

Applications

- Contaminated Environments
- Chemical Handling
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Opening and draining pumps valves or lines
- Loading and unloading of proces equipment
- Raw material sample collection
- Concentration mixing and palletisation
- Hazmat response
- Assembly and disassembly of large pipes
- Unexpected leakages spills or other releases



AlphaTec®

ADVANCED CHEMICAL PROTECTION

5000 - Model 122

Durable, highly visible, multi-layer chemical barrier technology, Type 3/4/5 protection

Previously known as: MICROCHEM® by AlphaTec® 5000 - Model 122

PRODUCT INFORMATION

| | |
|---------------------------|--|
| Design Features | Coverall with 2-piece hood, double zip closure, double cuffs with knitted inner cuff and attached socks with boot overflaps. Elasticated hood, waist, outer cuffs and boot overflaps. |
| Standards Overview | CE CATEGORY III (Type 3-B, Type 4-B, Type 5-B, EN 1073-2, EN 14126, EN 1149-5) |
| Product Reference | 5000 - Model 122 |
| Sizes | S-5XL (02-09) |
| Weight | 132gsm |

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

