



COMBINATION LADDER



HEAVY DUTY
BOOT
NON-MARRING
TREAD



FRONT SECTION
HAS 3" FLAT
STEP WITH
SLIP-RESISTANT
TREAD



PRO END CAP
NON-MARRING
HEAVY DUTY
PROTECTS SURFACE
FROM DAMAGE



WEB POLE GRIP



INNER BRACES



1-800-666-2811

www.LOUISVILLELADDER.com

* REAR SECTION WITH ROUND RUNGS

MODEL	LADDER SIZE	MAX. EXTENDED LENGTH	MAX. STANDING LEVEL		MAX. REACH		FLARED SECTION			
			STEPLADDER	EXTENSION	STEPLADDER	EXTENSION	MIN. OUTSIDE DIMENSION	MAX OUTSIDE DIMENSION	WEIGHT (LBS)	APPROX. CUBES
FXC1206	6'	9' 8"	3' 9"	5' 7"	10' 4"	12' 2"	17 1/2"	24 1/2"	34	7
FXC1207	7'	11' 8"	4' 8"	7' 6"	11' 3"	14' 1"	17 1/2"	25 1/2"	39	8.3
FXC1208	8'	13' 8"	5' 7"	9' 5"	12' 2"	16'	17 1/2"	26 1/2"	43	9.6

*OUTSIDE DIMENSION (ALL): 14 1/2"

