

3M[™] Specialty Tape Solutions

3M[™] Polyester Tape 850

For splicing applications requiring quick stick and an aggressive, permanent hold, use our 3M[™] Polyester Tape 850. Used in a variety of applications, including web processing, label protection, and marking. This tape is available in various colors, as well as a transparent.

Key Characteristics

- Thin caliper, high tensile strength and elongation at break for reliable butt and other splices
- Seal, protect and reinforce
- Color code or decorate with long term holding
- Maintains color after long term aging
- Transparent option for virtually invisible splices

Use For

- Film splicing
- Defect marking
- Edge reinforcement
- Sealing
- Color coding



Black	Technical Parameters	
Clear Red	Adhesive	Acrylic
	Backing	Polyester
	Backing Thickness	0.9 mils (0.02mm)
Silver	Total Thickness	1.9 mils (0.05mm)
White	Temperature Use Range	-60°F to 300°F (-50°C to 150°C)

Specialty Six

Bringing better ideas to the surface with a wide variety of tape solutions.

3M[™] Specialty Tape Solutions meeting application challenges for appliances, aerospace, automotive, construction, MRO, electronics, commercial transport, marine and more.



For more information, call 1-800-362-3550 or visit 3M.com/IATD



3M Industrial Adhesives and Tapes Division3M Center, Building 225-3S-06St. Paul, MN 55144-1000Phone800-362-3550Fax877-369-2923Web3M.com/IATD

Product Use: Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. Warranty, Limited Remedy and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price. Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, negligence or strict liability.

3M is a trademark of 3M. © 3M 2017. All rights reserved. Please recycle. Printed in USA. 70-0716-9837-0 3/2017