

DEWALT®

20V^{MAX*}
LITHIUM ION

LED LIGHTING
5,000 Lumens Max Output
Natural White LED

CORDLESS OPERATION
Compatible with all DEWALT 20V MAX*
and DEWALT FLEXVOLT® Batteries

RUNTIME: Up to 11 hours**

**Using DCB206 6.0 Ah 20V MAX*
Lithium Ion Battery on low setting.

GUARANTEED TOUGH®
Impact-resistant lens and
durable “roll cage” design

VARIABLE BRIGHTNESS
Fine-tune illumination for
your environment



MULTIPLE USES
Integrated hook for hanging
and tripod mount

TOOL CONNECT™
Track and control your lights
with the free mobile app

*Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by DEWALT is under license. Other trademarks and trade names are those of their respective owners.



**MANAGE YOUR TOOLS.
ANYWHERE.™**



PRODUCTS | FREE MOBILE APP | INVENTORY MANAGER

**TOOL CONNECT™ 20V MAX*
ALL-PURPOSE LIGHT**

DCL074



› Use hanging via hook for multiple lighting applications



› Use freestanding or tripod-mounted (tripod sold separately)

SPECIFICATIONS

Max Output	Up to 5,000 lumens
Runtime**	Up to 11 hours
Tool Weight (Tool Only)	8.6 lbs

**Using DCB206 6.0 Ah 20V MAX* Lithium Ion battery on low setting.

TOOL WARRANTY

3 YEAR <small>LIMITED WARRANTY</small>	1 YEAR <small>FREE SERVICE</small>	90 DAY <small>MONEY BACK GUARANTEE</small>
------------------------------------------------------------	--------------------------------------------------------	----------------------------------------------------------------



**MANAGE YOUR TOOLS.
ANYWHERE.™**

Tool Connect™ is a three-part inventory management solution designed to help you save time and money.

PRODUCTS

With integrated Bluetooth® technology



FREE MOBILE APP

Use the app to pair with Tool Connect™ assets on the jobsite



INVENTORY MANAGER

Inventory Manager Online Portal tracks your assets across multiple jobsites

DEWALT.COM/TC

RELATED TOOLS



DCL079
20V MAX* CORDLESS
TRIPOD LIGHT



DCL070
20V MAX* TOOL CONNECT™
CORDED/CORDLESS LED
AREA LIGHT



DCB206
20V MAX* PREMIUM
XR® 6.0 AH BATTERY



DCB612
DeWALT FLEXVOLT®
20V/60V MAX*
12.0 AH BATTERY

1-800-4-DEWALT

www.DEWALT.com

With respect to 20V MAX, maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.

**With respect to 60V MAX*, maximum initial battery voltage (measured without a workload) is 60 volts. Nominal voltage is 54.

Copyright ©2018 DEWALT. The following are trademarks for one or more DEWALT power tools, accessories, anchors and concrete adhesives: The yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.

DCL074SS