



# PLUS T8 High Output

## F96T8/TL841/HO/PLUS ALTO 25/1

Philips PLUS T8 High Output 8-foot fluorescent lamps reduce the impact on the environment by offering long life and low mercury.

### Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Base	R17D [ R17d (RDC)]
Life 3-Hr Start [Hrs]	24000 h
Features	ALTO® Plus
Footnotes Fluorescent/CFL 1	This Bulb Meets US Federal Minimum Efficiency Standard.

Light Technical	
Color Code	TL841 [ CCT of 4100K (841)]
Initial lumen (Nom)	8200 lm
Color Designation	TL841
Design Mean Lumens	7625 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	85

Operating and Electrical	
Power (Rated) (Nom)	86 W

Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	96
Bulb Shape	T8 [ T8 (T8)]


Approval and Application	
Energy Saving Product	Energy Saving
Picogram Per Lumen Hour	24 pg/lm.h
Mercury (Hg) Content (Nom)	4.4 mg

Product Data	
Order product name	F96T8/TL841/HO/PLUS ALTO 25/1
EAN/UPC - Product	046677236885
Order code	236885
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927874084105
Net Weight (Piece)	0.001 kg

PLUS T8 High Output

Dimensional drawing

Product
F96T8/TL841/HO/PLUS ALTO 25/1



F96T8 86W/841 HO ALTO Plus ES

