



High CRI T12

F96T12/CW Supreme/ALTO 15PK

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Approval and Application	
Base	FA8 [FA8]	Nominal Length (Inch)	96
Life 3-Hr Start [Hrs]	12000 h	Bulb Shape	T12 [T12 (T12)]
Features	ALTO® (ALTO)	Energy Saving Product	Energy Saving
Light Technical		Mercury (Hg) Content (Nom)	6.8 mg
Initial lumen (Nom)	5000 lm	Product Data	
Color Designation	Cool White Supreme	Order product name	F96T12/CW Supreme/ALTO 15PK
Design Mean Lumens	4250 lm	EAN/UPC - Product	046677423193
Correlated Color Temperature (Nom)	4100 K	Order code	423194
Color Rendering Index (Nom)	89	Numerator - Quantity Per Pack	1
Operating and Electrical		Numerator - Packs per outer box	15
Power (Rated) (Nom)	75 W	Material Nr. (12NC)	927895003704
Mechanical and Housing		Net Weight (Piece)	0.442 kg
Cap-Base Information	Green Base		

High CRI T12

Dimensional drawing

Product

F96T12/CW Supreme/ALTO 15PK



F96T12 CW Supreme ALTO®

