



High CRI T12

F40T12/CWSupreme/ALTO

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

Warnings and Safety

• Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
Life 3-Hr Start [Hrs]	20000 h
Life 12-Hr Start [Hrs]	24000 h
Features	ALTO® (ALTO)
System Description	Rapid Start (RS)

Light Technical	
Initial lumen (Nom)	2600 lm
Color Designation	Cool White Supreme
Design Mean Lumens	2250 lm
Correlated Color Temperature (Nom)	4100 K
Color Rendering Index (Nom)	89

Operating and Electrical	
Power (Rated) (Nom)	40 W

Mechanical and Housing	
Cap-Base Information	Green Base

Nominal Length (Inch)	48
Bulb Shape	T12 [T12 (T12)]

Approval and Application	
Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg


Product Data	
Order product name	F40T12/CWSupreme/ALTO
EAN/UPC - Product	046677423889
Order code	423889
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	927887803901
Net Weight (Piece)	0.230 kg

High CRI T12

Dimensional drawing

Product

F40T12/CWSupreme/ALTO



F40T12 CW Supreme ALTO

