

SlipFit® cuff assists a quick on and off between tasks

Superior wet/dry grip and abrasion resistance

Synthetic leather palm

HPPE blend liner provides 360° industry-leading cut resistance (interior layer)

Reinforced Seams

Hi-vis color on back-of-hand

High dexterity

Form-fitting, quality materials

Launderable



4072 Chrome SLT® 360°

PROTECTION ZONES:

HPPE blend Liner

ANSI/ISEA CUT	GRAM SCORE
A6	3011
ANSI/ISEA PUNCTURE	UK CE
3	3X42F

FEATURES:

HexArmor® Chrome SLT® gloves are built for a wide array of applications. Each product in the series was crafted to fit the hand with a specific purpose. With multiple styles and various safety features, you can be confident that the Chrome SLT® will keep your hands protected against almost any hazard. Our Chrome SLT® gloves were designed with ultimate comfort in mind, providing unsurpassed dexterity while maintaining cut and puncture resistance. With options for cold weather protection, your hands can stay safe and comfortable in any environment.

ATTRIBUTES:

Style:	Mechanics
Grip:	Wet or Dry
Cuff Style:	SlipFit®
Sizes:	6/XS through 12/3XL

HexArmor®

Call **1-877-MY ARMOR** or visit **hexarmor.com**

HexArmor® products are cut and puncture resistant, NOT CUT AND PUNCTURE PROOF. Do not use with moving or serrated blades or tools. User shall be exclusively responsible to assess the suitability of the product as specified for any individual application or use. Protection zones are to be used as a general guide. Actual product protection zones may differ. Product features, design, protection zones subject to change.

Protected by patents and patents pending