



**MCR
SAFETY**

5015 SensaGuard Disposable Specification Sheet

PRODUCT DESCRIPTION:

These industrial grade disposables are suited for lots of applications and can be employed for basic household cleanup tasks, food processing or light industrial work. These could include washing dishes, using common cleaning chemicals or having to put the hands in contact with hair dyes. They do protect the hands from direct exposure to various things that might create illness or cause skin breakout. They are latex free.

FEATURES:

- 5 mil, powder free vinyl
- Component materials comply with all federal regulations for food contact
- Industrial Grade
- 9.5 inch

APPLICATIONS:

Dentistry, Electronic Assembly, Food service, Cafeteria



TECHNICAL DATA FOR: 5015

Series	SensaGuard	Overall Length	9.5 in.
Material Group	Unsupported	FDA Accepted Materials	FDA Compliant
Product Type	Disposable		
Glove Size	Large		
Material	Vinyl		
Grade	Premium		
Features	Reversible		
Lining	Unlined		
Pattern	Reversible		
Thumb Style	Wing		

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved



MCR
SAFETY

5015

SensaGuard

Disposable

Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
5015L	Large	10.197	5.315	N/A	15.280 lb.	15.280
5015M	Medium	9.960	4.921	N/A	14.007 lb.	14.007
5015S	Small	9.606	4.134	N/A	12.620 lb.	12.620
5015XL	X - Large	10.622	6.457	N/A	16.180 lb.	16.180

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2018 MCR Safety - All Rights Reserved