

*American
Standard*

americanstandard.com

CADET[®] PRO[™]



**THE FULL PORTFOLIO CADET LINE WITH TRADE EXCLUSIVE
STYLES AND FEATURES**

- Trade exclusive toilet styles and features
- Cadet PRO has robust metal parts not found on products at the big box stores
- Save time with EZ-Install installation kits included at no extra cost
- Full portfolio of 5 bowls and 5 tanks

Compare the Cadet PRO differences versus other brands:


	CADET PRO	OTHER BRANDS
A FLUSH VALVE	3" Diameter	2" to 3" Diameter
B SIPHON OUTLET	2-1/8"	2" to 2-1/8"
C WATER SPOT	9" x 8"	8" to 10" x 7" to 9"
D BOWL RINSE	PowerWash®	Standard†
SURFACE	Standard with EverClean	Ordinary surface
MAP* SCORE	BEST 1,000 g	400 - 1,000 g
WARRANTY	5 Years (covers chinaware and trim)	1 Year



CHINWARE COLORS



TRIP LEVER FINISHES (CHROME COMES STANDARD)



BOWL SHAPE	BOWL MODEL	BOWL HEIGHT	ROUGH-IN	Cadet PRO		Tropic® Cadet PRO		Studio® Cadet PRO		Triangle Cadet PRO	
				COMBO MODEL	TANK MODEL	COMBO MODEL	TANK MODEL	COMBO MODEL	TANK MODEL	COMBO MODEL	TANK MODEL
RIGHT HEIGHT® ELONGATED	3517A	16-1/2"	12"	215AA	4188A	217AA	4190A	218AA	4191A	216AD	4189D
		16-1/2"	10"	215AB	4188B						
RIGHT HEIGHT ROUND FRONT	3517B	16-1/2"	12"	215BA	4188A	217BA	4190A	218BA	4191A	216BD	4189D
		16-1/2"	10"	215BB	4188B						
ELONGATED	3517C	15"	12"	215CA	4188A	217CA	4190A	218CA	4191A		
		15"	10"	215CB	4188B						
ROUND FRONT	3517D	15"	12"	215DA	4188A	217DA	4190A	218DA	4191A		
		15"	10"	215DB	4188B						
COMPACT RIGHT HEIGHT ELONGATED	3517F	16-1/2"	12"	215FA	4188B						
		16-1/2"	14"	215FC	4188A						

1.28 gpf/4.8 Lpf Water Usage Tanks‡

TANK SKU	TANK DESCRIPTION	CHINWARE COLORS
4188A.104	12" Tank	020, 021, 222, 178
4188A.105	Tank with RHTL	020
4188A.154	Tank with liner	020, 021, 222, 178
4188A.155	Tank with liner and RHTL	020
4188A.164	Tank with TCLD	020
4188A.165	Tank with TCLD and RHTL	020
4188A.174	Tank with TCLD and liner	020
4188B.104	10" Tank	020, 021, 222
4188B.105	10" Tank with RHTL	020
4190A.104	Tropic Tank	020, 222
4191A.104	Studio Tank	020, 021, 222

RHTL = Right Hand Trip Lever

TCLD = Tank Cover Lock Device

1.6 gpf/6.0 Lpf Water Usage Tanks

TANK SKU	TANK DESCRIPTION	CHINWARE COLORS
4188A.004	12" Tank	020, 021, 222, 178
4188A.005	Tank with RHTL	020
4188A.054	Tank with liner	020, 021, 222
4188A.064	Tank with TCLD	020
4188A.065	Tank with TCLD and RHTL	020
4188A.074	Tank with TCLD and liner	020
4188B.004	10" Tank	020, 021, 222
4188B.005	10" Tank with RHTL	020
4189D.004	Triangle Tank	020, 021, 222

Cover: 215AA Right Height Elongated Toilet

* Maximum Performance (MaP) testing performed by IAPMO R&T Lab. MaP Report conducted by Veritec Consulting, Inc. and Koeller and Company.

† Gravity flow through rim punchings.

‡ High Efficiency, ultra-low consumption 1.28 gpf (4.8 Lpf) models utilize 20% less water and meet EPA WaterSense® criteria.

